

TECHNICAL DATA

Fluke Wide-Angle Infrared Lens



Key features

Field-of-View (FOV) is 42.5° x 32.5°

Product overview: Fluke Wide-Angle Infrared Lens

Optional, field swappable, wide angle thermal lens allows the user to have a wider field of view for working in tight spaces.

Ordering information



Fluke Lens/Wide1

Wide-angle Infrared Lens

For use with: Ti32 and TiR32

Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Europe/M-East/Africa
+31 (0)40 267 5100
In Canada (800)-36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com/en-th

©2021 Fluke Corporation. Specifications subject to
change without notice.
12/2021

**Modification of this document is not permitted
without written permission from Fluke Corporation.**