

TECHNICAL DATA

# P5543 Angle Adapter



## Product overview: P5543 Angle Adapter

To calibrate gauges with the pressure connection on the rear (e.g. panel mount gauges) in their correct operating position, an angle adaptor should be used. The angle adaptor uses the standard gauge adapters and positions the gauges at 90°. The maximum working pressure of this unit is 10,000 psi (700 bar).

## Specifications: P5543 Angle Adapter

Specifications	
Body materials	Stainless steel
O-Rings	Nitrile
Test Port Adapters	As supplied with calibrator
Calibrator Connection	3/8 BSP male (mating adapter supplied)

## Ordering information

**P5543**

P5543 Angle Adapter

---

Angle Adapter

---

**Fluke.** *Keeping your world up and running.®*

**Fluke Corporation**  
PO Box 9090, Everett, WA 98206 U.S.A.

**For more information call:**  
In the U.S.A. (800) 443-5853  
In Europe/M-East/Africa  
+31 (0)40 267 5100  
In Canada (800)-36-FLUKE  
From other countries +1 (425) 446-5500  
[www.fluke.com/en-th](http://www.fluke.com/en-th)

©2022 Fluke Corporation. Specifications subject to  
change without notice.  
01/2022

**Modification of this document is not permitted  
without written permission from Fluke Corporation.**