

TECHNICAL DATA

Fluke Networks MT-8200-61-TNR IntelliTone™ Pro 200 Tone Generator



Key features

- Verifies and troubleshoots copper cabling, service and continuity
- Kit includes IntelliTone™ Pro 200 Toner, adapters, patch cables, test leads
- SmartTone analog signals for locating cabling on active networks
- Four distinct cadences for isolating individual wire pairs
- Supports VDV cable types inc. RJ45/11, coax, bare wire

Product overview: Fluke Networks MT-8200-61-TNR IntelliTone™ Pro 200 Tone Generator

Digital and analog tone generator verifies and troubleshoots copper cabling in networks—identifying the type of service and verifying continuity. F-type connector supports VDV cables: RJ45, RJ11, coaxial, bare wire, banana jacks/test leads. Diagnoses 10/100 Gigabit Ethernet link connectivity with NIC/hub indication.

Specifications: Fluke Networks MT-8200-61-TNR IntelliTone™ Pro 200 Tone Generator

General specifications

Operating temperature	32 °F to 104 °F (0 °C to 40 °C)
Storage temperature	-4 °F to +140°F (-20 °C to °C)
Operating relative humidity (% RH without condensation)	95 % (50 °F to 95 °F; 10 °C to 35 °C) 75 % (95 °F to 104 °F; 35 °C to 40 °C) Uncontrolled < 50 °F (< 10 °C)
Vibration	Random, 2 g, 5 Hz-500 Hz
Shock	1 m drop test
Safety	EN 61010-1, Category: None
Altitude	3000 m
EMC	EN 61326-1, FCC Part 15 B
Battery type and life	9 V alkaline (NEDA 1604A or IEC 6LR61); 20 hours typical
Applications	Copper cabling media including; 75 or 50 Ohm Coaxial cable; Two Conductor control, security, generic cabling. 10 Base-T or 10/100 Base-T datacom networks. UTP cable. Shielded Twisted Pair supported in Cable Map function of the IntelliTone 200.

Toner specifications

Dimensions	5.54 in x 2.94 in x 1.25 in (14.1 cm x 7.5 cm x 3.2 cm)
Display	LED
Control	Thumbwheel switch
Toner interface	Main Mod8 port for tone generation on all 4 pairs of UTP / STP cabling. F Connector for coaxial cabling Banana Jack Plugs (2) - two conductor wiring
Toner frequency	"IntelliTone™ signal: encoded digital signal Analog SmartTone signal: 500 - 1200Hz, 4 songs"
Ouptut power	5 V p-p
Auto power down	Turns off automatically after 2 1/2 hours of inactivity



Fluke. *Keeping your world up and running.*®

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Europe/M-East/Africa
+31 (0)40 267 5100
In Canada (800)-36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com/en-th

©2022 Fluke Corporation. Specifications subject to
change without notice.
01/2022

**Modification of this document is not permitted
without written permission from Fluke Corporation.**