

TECHNICAL DATA

Fluke 787CAL Calibration Module

Key features

Application: The calibration module provides a 9 volt dc supply to the 787. At the same time, it facilitates RS232 communication from the PC running MET/CAL to the 787 over the battery leads of the 787.

Product overview: Fluke 787CAL Calibration Module

Description: The Fluke 787CAL module permits users and service facilities to perform automated MET/CAL verifications and calibrations of the Fluke 787 ProcessMeter.

Note: An installation of MET/CAL Calibration Software plus appropriate calibration hardware must be provided by the user.

Ordering information

Fluke 787CAL

Fluke 787CAL Calibration Module
Calibration Module

Included:

- A calibration manual
 - MET/CAL procedures
 - An interface module that permits serial communication between a 787 and a PC.
-

Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Canada (800) 36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com

©2021 Fluke Corporation.
Specifications subject to change without notice.
12/2021

**Modification of this document is not permitted
without written permission from Fluke Corporation.**