

TECHNICAL DATA

Fluke C25 Large Soft Case for DMMs



Key features

- Zippered carrying case with padding and inside pocket
- Dimensions 218 x 128 x 64 mm (8.6 x 5 x 2.52 in)
- Convenient belt loop for hands-free carrying

Product overview: Fluke C25 Large Soft Case for DMMs

Protect your Fluke meters with our most popular zippered carrying case sold to date. This durable case is made with a high-quality polyester exterior and features padding on the interior pocket.

If you're looking for a Fluke case for meters like your 117, 115 or for your 87V, the C25 is designed for those multimeters. It is recommended to be used with most mid-sized multimeters, process and temperature meters. Some meters this Fluke case is compatible with:

- [Fluke 323 True RMS Clamp Meter](#)
- [Fluke 324 True-RMS Clamp Meter with Temperature & Capacitance](#)
- [Fluke 87V IMSK Industrial Multimeter Service Combo Kit](#)
- [Fluke 114 Electrical Multimeter](#)
- [Fluke 115 Field Technicians Digital Multimeter](#)
- [Fluke 116 Digital HVAC Multimeter](#)
- [Fluke 117 Electrician's Multimeter with Non-Contact Voltage](#)

"...ample room for the quick reference card, the meter, and the leads (...) the material quality and construction should take abuse while protecting your expensive meter"- Jabit, verified customer

Specifications: Fluke C25 Large Soft Case for DMMs

Dimensions (H x W x D)
218 x 128 x 64 mm
8.6 x 5 x 2.52 in

Ordering information



Fluke C25

Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Canada (800) 36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com

©2022 Fluke Corporation.
Specifications subject to change without notice.
01/2022

**Modification of this document is not permitted
without written permission from Fluke Corporation.**