

TECHNICAL DATA

Fluke 90i-610s 1A to 600A AC/DC Current Probe



Product overview: Fluke 90i-610s 1A to 600A AC/DC Current Probe

The 90i-610s is a clamp-on AC/DC Current Probe designed to measure current waveforms in automotive applications with any Test Tool capable of millivolt measurements. There are two measurement ranges: 0 to 100 A (output voltage 10 mV/A) and 0 to 600 A (output voltage 1 mV/A).

Specifications: Fluke 90i-610s 1A to 600A AC/DC Current Probe

Specifications	
Current range	1 to 600 A DC or AC Peak
Basic accuracy	(DC to 400 Hz): $\pm(2\%$ of reading + 1 A)
Output signal	100 A range: 10 mV/A 600 A range: 1 mV/A
Frequency range	40 Hz to 400 Hz
Working voltage	600 V AC rms
Maximum conductor diameter	34 mm (1.34 in)
Safety Rating	IEC 1010 and CSA-C22.2 No. 1010-1 Installation Category II, Working Voltage 600 V

Ordering information



Fluke 90i 610s

1A to 600A AC/DC Current Probe

Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Canada (800) 36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com

©2022 Fluke Corporation.
Specifications subject to change without notice.
01/2022

**Modification of this document is not permitted
without written permission from Fluke Corporation.**