

## TECHNICAL DATA

## Fluke EI-1625 Selective/Stakeless Clamp Set for Fluke 1625



### Product overview: Fluke EI-1625 Selective/Stakeless Clamp Set for Fluke 1625

The Selective/Stakeless clamp set is used along with the Fluke 1625 to perform selective and stakeless testing. Selective testing means using one clamp along with earth ground stakes to provide earth ground loop resistance values for one earth ground electrode. Stakeless testing uses both clamps provided to perform earth ground loop resistance measurement without stakes. Both tests have the advantage of providing measurements with no disconnection from the grounding system! Safer and quicker. Already included in the Fluke 1625 Kit. Both clamps have a 50.8 mm (2-inch) inner diameter.

## Ordering information



### **EI-1625**

Fluke EI-1625 Selective/Stakeless Clamp Set for Fluke 1625  
Selective/Stakeless Clamp Set for Fluke 1625

---

**Fluke.** *Keeping your world up and running.®*

**Fluke Corporation**  
PO Box 9090, Everett, WA 98206 U.S.A.

**For more information call:**  
In the U.S.A. (800) 443-5853  
In Canada (800) 36-FLUKE  
From other countries +1 (425) 446-5500  
[www.fluke.com](http://www.fluke.com)

©2021 Fluke Corporation.  
Specifications subject to change without notice.  
12/2021

**Modification of this document is not permitted  
without written permission from Fluke Corporation.**