


TECHNICAL DATA

Fluke MBX 300 Poleset Mounting Kit



Product overview: Fluke MBX 300 Poleset Mounting Kit

Built with all-weather IP65 enclosures, the Fluke 1743 and 1744 Power Quality Loggers are ready to be installed wherever the job demands. With the durable mounting kit, the Fluke 1743 and 1744 can be easily and safely secured to utility poles or suspended from other hardware. The package includes a mounting plate and strap that affix with existing fasteners and attachment points on the loggers.

Ordering information



Fluke MBX 300 Poleset Mounting Kit

Fluke MBX 300 Poleset Mounting Kit

Built with all-weather IP65 enclosures, the Fluke 1743 and 1744 Power Quality Loggers are ready to be installed wherever the job demands. With the durable mounting kit, the Fluke 1743 and 1744 can be easily and safely secured to utility poles or suspended

Fluke 1743/44 Poleset

Fluke MBX 300 Poleset Mounting Kit

Fluke MBX Clamp 1A/10A

Fluke Set of 3 1A/10A Current Clamps

Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Canada (800) 36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com

©2021 Fluke Corporation.
Specifications subject to change without notice.
11/2021

**Modification of this document is not permitted
without written permission from Fluke Corporation.**