

TECHNICAL DATA

Fluke TLK282 SureGrip™ Deluxe Automotive Test Lead Kit



Key features

Everything you can find in the TLK281 Automotive Test Lead Kit, plus a few extras. Use the back probe pins to slide into weather pack connectors on fuel injectors, TPS and MAP sensors. A hook probe with plunger actuation allows quick connection to pins or exposed conductors.

- Tested to 60 V DC

Product overview: Fluke TLK282 SureGrip™ Deluxe Automotive Test Lead Kit

Everything you can find in the TLK281 Automotive Test Lead Kit, plus a few extras. Use the back probe pins to slide into weather pack connectors on fuel injectors, TPS and MAP sensors. A hook probe with plunger actuation allows quick connection to pins or exposed conductors.

Ordering information



Fluke TLK282

SureGrip™ Deluxe Automotive Test Lead Kit

Kit contains:

- TP81 Insulation Piercing Clip Set
- TP40 Automotive Back Probe Pins (five)
- TL224 Suregrip™ Silicone Test Lead Set
- TP220 Suregrip™ Test Probe Set
- AC220 Suregrip™ Alligator Clip Set
- AC285 Suregrip™ Large Jaw Alligator Clip Set
- AC280 Suregrip™ Hook Clip Set
- Soft Case



Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Canada (800) 36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com

©2021 Fluke Corporation.
Specifications subject to change without notice.
12/2021

**Modification of this document is not permitted
without written permission from Fluke Corporation.**