

## TECHNICAL DATA

# Fluke Ergonomic Bottle Opener



## Key features

- Professional refreshment tool
- Soft grip, ergonomic anti-roll handle for easy storage
- High-quality stainless-steel construction
- German engineered and produced
- Not an insulated tool; not to be used near live electrical circuits

## Product overview: Fluke Ergonomic Bottle Opener

This bottle opener is a must have for the kitchen, bar, workshop, or truck. The only bottle opener to feature a design like the Fluke Ergonomic Hand Tools. It includes a 2-component grip, hexagonal “no-roll” handle along with a hole in the handle for hanging storage.

The Fluke Ergonomic Bottle Opener is a high-quality, German-engineered product. For top-of-the-line ergonomics and a secure transmission of force, this bottle opener will insure a safe, reliable way to open your favorite beverage.

Note – Not an insulated tool; not to be used near live electrical circuits.

## Ordering information



### INS-BOT

Fluke ergonomic bottle opener, single

#### Optional accessories

#### Description

**Fluke CPAK Magnetic Hanging Tool Pouch** Keep your tools together and within reach in your tool bag.

**Fluke Pack30 Professional Tool Backpack** The Fluke Pack30 tool backpack gives you a comfortable hands-free experience vs. traditional tool belts that put all the weight on your lower back.

**Fluke C25 Large Soft Case for DMMs** Fits most mid-sized multimeters, process and temperature meters.



**Fluke.** *Keeping your world up and running.®*

**Fluke Corporation**  
PO Box 9090, Everett, WA 98206 U.S.A.

**For more information call:**  
In the U.S.A. (800) 443-5853  
In Canada (800) 36-FLUKE  
From other countries +1 (425) 446-5500  
[www.fluke.com](http://www.fluke.com)

©2021 Fluke Corporation.  
Specifications subject to change without notice.  
12/2021

**Modification of this document is not permitted  
without written permission from Fluke Corporation.**