

TECHNICAL DATA

## PLS WCB10



### Product overview: PLS WCB10

The PLS WCB10 is a metallic rotary wall and ceiling mount for all PLS rotary laser levels. The WCB10 is included with the PLS HV2R and PLS HV2G System and Kit configurations.

## Ordering information



### **PLS WCB10**

The PLS WCB10 is a metallic rotary wall and ceiling mount for all PLS rotary laser levels. The WCB10 is included with the PLS HV2R and PLS HV2G System and Kit configurations.

---

#### Contents:

- PLS WCB10 Rotary Wall and Ceiling Mount
  - Quick Reference Guide
-

**Fluke.** *Keeping your world up and running.®*

**Fluke Corporation**  
PO Box 9090, Everett, WA 98206 U.S.A.

**For more information call:**  
In the U.S.A. (800) 443-5853  
In Canada (800) 36-FLUKE  
From other countries +1 (425) 446-5500  
[www.fluke.com](http://www.fluke.com)

©2021 Fluke Corporation.  
Specifications subject to change without notice.  
11/2021

**Modification of this document is not permitted  
without written permission from Fluke Corporation.**