

Fluke TLK290 Flexible Socket Probe Set



Key features

- Test probe set to be used on motor and three phase sockets
- Probes have flexible test points that fits securely between 4 and 8 mm sockets
- For use with 4 mm shrouded test leads, such as Fluke TL224
- Safe contact e.g. in CEE 16 A und CEE 32 A plugs
- Probe CAT II 1000V, 8A; Alligator CAT III 1000V, 16A

Product overview: Fluke TLK290 Flexible Socket Probe Set

Set includes three Flexible Socket Probes and a Large Alligator Clip.

Ordering information



Fluke TLK290

Optional accessories

Fluke 3PHVL-17XX and 3PHVL-17XX-5M Voltage Test Lead Sets

Description

Flat, three-phase voltage connection cable for the Fluke Power and Energy Loggers.



Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Canada (800) 36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com

©2021 Fluke Corporation.
Specifications subject to change without notice.
11/2021

**Modification of this document is not permitted
without written permission from Fluke Corporation.**