

TECHNICAL DATA

# Fluke 80T-IR/E Extended Range Infrared Surface Temperature Probe



## Product overview: Fluke 80T-IR/E Extended Range Infrared Surface Temperature Probe

The 80T-IR/E is compatible with any DMM with 10 MOhms input impedance, standard diameter banana jacks, and mV dc capability. Ideal for maintenance applications where object to be measured is hazardous to touch, is moving, easily contaminated, or difficult to reach.

## Ordering information



### **80T-IR/E**

Fluke 80T-IR/E Extended Range Infrared Surface Temperature Probe

---

**Fluke.** *Keeping your world up and running.®*

**Fluke Corporation**  
PO Box 9090, Everett, WA 98206 U.S.A.

**For more information call:**  
In the U.S.A. (800) 443-5853  
In Canada (800) 36-FLUKE  
From other countries +1 (425) 446-5500  
[www.fluke.com](http://www.fluke.com)

©2021 Fluke Corporation.  
Specifications subject to change without notice.  
12/2021

**Modification of this document is not permitted  
without written permission from Fluke Corporation.**