

TECHNICAL DATA

## Fluke 1730-TL2M Test Lead Set



### Product overview: Fluke 1730-TL2M Test Lead Set

2 m test lead for connecting measurement input to the Fluke 1730 Energy Logger.

## Ordering information



### **Fluke 1730-TL2M**

1000 V CAT III; straight plug; 2 m; PVC red/black

---



**Fluke.** *Keeping your world up and running.®*

**Fluke Corporation**  
PO Box 9090, Everett, WA 98206 U.S.A.

**For more information call:**  
In the U.S.A. (800) 443-5853  
In Canada (800) 36-FLUKE  
From other countries +1 (425) 446-5500  
[www.fluke.com](http://www.fluke.com)

©2021 Fluke Corporation.  
Specifications subject to change without notice.  
12/2021

**Modification of this document is not permitted  
without written permission from Fluke Corporation.**