

TECHNICAL DATA

Fluke STL90 Shielded Test Lead Set



Key features

- Two shielded test leads:
 - Cable length: 1.5 m
 - Safety designed shrouded banana input
 - Safety designed insulated BNC connector
 - Maximum signal voltage: 300 V
 - Maximum voltage to ground: 600 V per IEC 1010-2-031 CAT III
 - Maximum current 3 A
- Two Ground leads:
 - Cable length: 250 mm
 - Maximum current 3 A
 - Safety designed shrouded banana jacks
- Two 4 mm Tip adapters, 30 V
- Two 2 mm Tip adapters, 30 V
- Three backprobe pins, 30 V, 1 A
- Two insulated Alligator Clips (AC85A)
- One year warranty

Product overview: Fluke STL90 Shielded Test Lead Set

Industrial shielded, 1:1, silicone insulated test lead set. Useful bandwidth 1 MHz. Silicone insulated leads won't crack from cold or melt from accidental contact with hot surfaces. Superior strain relief and flexibility provide extra long life. Compatible with Fluke ScopeMeter Test Tools.

Ordering information



Fluke STL90

Fluke STL90 Shielded Test Lead Set

Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Canada (800) 36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com

©2021 Fluke Corporation.
Specifications subject to change without notice.
11/2021

**Modification of this document is not permitted
without written permission from Fluke Corporation.**