

TECHNICAL DATA

Fluke TL26A 60 in. 5-Way Test Lead Set



Product overview: Fluke TL26A 60 in. 5-Way Test Lead Set

5 ways to connect:

1. U-shaped nose for blade-shaped terminals
2. Notched jaw for gripping screw heads, bare wire or terminals
3. Serrated teeth for gripping threaded or wire-wrapped terminals
4. Cluster of sharp needles for piercing small gauge (#22-#28 AWG) wires
5. Large piercing needle for penetrating larger gauge wires

Ordering information



Fluke TL26A

60" (1.5m), silicone-insulated leads, useable from -80 °C to +70 °C (-112 °F to +158 °F). Rated for 30V, 8A. One red, one black.

Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Canada (800) 36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com

©2021 Fluke Corporation.
Specifications subject to change without notice.
11/2021

**Modification of this document is not permitted
without written permission from Fluke Corporation.**