

# Fluke TL28A Automotive Test Lead Set



## Key features

- Flexible silicone insulated leads are heat and cold resistant
- Cat I 30 V, 10 A

## Product overview: Fluke TL28A Automotive Test Lead Set

Large jaws, long leads and a piercing needle inside the jaws. Solid, spring-loaded copper clips with a wide 12.7 mm (.50") jaw opening and serrated teeth. Large piercing needle for penetrating larger gauge wires located inside the jaws. 1.5 m (60"), silicone-insulated leads, useable from -80 °C to +70 °C (-112 °F to +158 °F). Rated for 30 V, 10 A. One red, one black.

## Ordering information



**Fluke TL28A**

**Fluke.** *Keeping your world up and running.®*

**Fluke Corporation**  
PO Box 9090, Everett, WA 98206 U.S.A.

**For more information call:**  
In the U.S.A. (800) 443-5853  
In Canada (800) 36-FLUKE  
From other countries +1 (425) 446-5500  
[www.fluke.com](http://www.fluke.com)

©2021 Fluke Corporation.  
Specifications subject to change without notice.  
11/2021

**Modification of this document is not permitted  
without written permission from Fluke Corporation.**