

TECHNICAL DATA

Fluke SVS-500 Shaft Voltage Measurement Kit



Product overview: Fluke SVS-500 Shaft Voltage Measurement Kit

The Fluke SVS-500 Shaft Voltage Measurement kit is designed for use with the Fluke MDA-500 Series Motor Drive Analyzers, and Fluke 190 Series ScopeMeter® Portable Oscilloscopes. The SVS-500 includes a set of 3 carbon fiber brushes, a probe holder with extension rods, and a magnetic base for securely mounting the measurement probes on the motor while measuring shaft voltage

Ordering information



Fluke SVS-500 Shaft Voltage Measurement Kit

Fluke SVS-500 Shaft Voltage Measurement Kit

- Three carbon fiber shaft voltage brushes
- Two-piece probe extension rod
- Magnetic mounting base

Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Canada (800) 36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com

©2021 Fluke Corporation.
Specifications subject to change without notice.
12/2021

**Modification of this document is not permitted
without written permission from Fluke Corporation.**