

## TECHNICAL DATA

# Fluke TP84 Oxygen Sensor Insulation Piercing Clip



## Key features

- Banana jack accepts all DMM and banana jack leads
- Non-rotating banana jack prevents leads from tangling, allowing you to tighten/loosen clamp while still connected to the test lead
- Tested to 60 V DC

## Product overview: Fluke TP84 Oxygen Sensor Insulation Piercing Clip

Long (30 cm, 12") piercing probe extends your reach into a hot engine. This long probe keeps your hands away from the exhaust manifold. The insulated body of the probe protects it from burning on a hot manifold.

## Ordering information



**Fluke TP84 Oxygen Sensor Insulation Piercing Clip**

---

**Fluke.** *Keeping your world up and running.®*

**Fluke Corporation**  
PO Box 9090, Everett, WA 98206 U.S.A.

**For more information call:**  
In the U.S.A. (800) 443-5853  
In Canada (800) 36-FLUKE  
From other countries +1 (425) 446-5500  
[www.fluke.com](http://www.fluke.com)

©2021 Fluke Corporation.  
Specifications subject to change without notice.  
12/2021

**Modification of this document is not permitted  
without written permission from Fluke Corporation.**