

TECHNICAL DATA

Macro Infrared Lens RSE



Product overview: Macro Infrared Lens RSE

Close up macro lens (0.5x) for inspection and analysis of even smaller subjects in research and development applications.

Applications: Research and development, extremely small targets, PCB boards (heat dissipation), semiconductor substrates, and seals.

Compatible with RSE300, RSE600.

Specifications: Macro Infrared Lens RSE

Description	
Object size	11 mm x 8.25 mm
Focus distance	10.8 mm +/- 1 mm (0.4 in)



Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Canada (800) 36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com

©2021 Fluke Corporation.
Specifications subject to change without notice.
12/2021

**Modification of this document is not permitted
without written permission from Fluke Corporation.**