

TECHNICAL DATA

4x Telephoto Infrared Smart Lens RSE



Product overview: 4x Telephoto Infrared Smart Lens RSE

View your target magnified 4 times more than a standard lens while staying on the ground or a safe distance away. A 4x telephoto lens can help identify a potential issue in your equipment, even when your target is as tiny and distant as a failed splice on a high electrical line or an overheated refractory on a tall flare stack.

- Avoid the hassle of sending in your camera to calibrate with the lens - with smart lenses you can just attach the lens to any compatible camera and start taking images.
- This lens includes a patent-pending lens attachment system that holds the lens securely in place, reducing lens wobble.
- Made of 100 % diamond-turned germanium with an engineered coating, the most efficient available material to transmit energy to the detector.

Compatible with RSE300, and RSE600.

Specifications: 4x Telephoto Infrared Smart Lens RSE

Description		
IFOV (spatial resolution)	RSE600	0.24 mRad
	RSE300	0.48 mRad
Field of view	6.0° H x 4.5° V	
Focus distance	1.5 m (approximately 5 ft)	



Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Canada (800) 36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com

©2021 Fluke Corporation.
Specifications subject to change without notice.
11/2021

**Modification of this document is not permitted
without written permission from Fluke Corporation.**