

TECHNICAL DATA

PLS RC2



Product overview: PLS RC2

The PLS RC2 Rotary Laser Remote Control is designed for the PLS HV2R and PLS HV2G rotary laser levels. This accessory comes shipped in a generic cardboard box with label.

Specifications: PLS RC2

Specifications:

- Range: 50 feet
- Remote Type: IR

Ordering information



PLS RC2

Contents:

- RC2 Rotary Laser Remote Control
- battery

Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Canada (800) 36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com

©2021 Fluke Corporation.
Specifications subject to change without notice.
11/2021

**Modification of this document is not permitted
without written permission from Fluke Corporation.**