

## TECHNICAL DATA

**PLS XLD****Product overview: PLS XLD**

The PLS XLD is a red and green rotary laser detector for use with all PLS rotary lasers. This accessory comes shipped in a printed cardboard box.

**Specifications: PLS XLD**

Specifications:

- Range: ≤600 m (2000 ft)
- Battery: 1x AA Alkaline
- Size: 135 mm x 69 mm x 25 mm (5.3 in x 2.7 in x 1.0 in)
- Weight: 0.19 kg (0.42 lb)

## Ordering information



### **PLS XLD**

The PLS XLD is a red and green rotary laser detector for use with all PLS rotary lasers. This accessory comes shipped in a printed cardboard box.

---

#### Contents:

- PLS XLD Rotary Laser Detector
  - PLS XLD Clamp
  - AA Battery
  - Quick Reference Guide
-



**Fluke.** *Keeping your world up and running.®*

**Fluke Corporation**  
PO Box 9090, Everett, WA 98206 U.S.A.

**For more information call:**  
In the U.S.A. (800) 443-5853  
In Canada (800) 36-FLUKE  
From other countries +1 (425) 446-5500  
[www.fluke.com](http://www.fluke.com)

©2021 Fluke Corporation.  
Specifications subject to change without notice.  
11/2021

**Modification of this document is not permitted  
without written permission from Fluke Corporation.**