

TECHNICAL DATA

Fluke 2062 Advanced Pro Wire Tracer Kit



Key features

- Locate energized and de-energized wires quickly and accurately in walls, ceilings, and floors
- Patented Smart Sensor™ locates and displays energized wires on color display
- Find breaks or opens and shorts, and identify breakers and fuses easily
- CAT IV 600 V safety rated
- Includes the i400 AC Current Clamp accessory for inducing a tracing signal on the cable when there is no access to bare conductors

Product overview: Fluke 2062 Advanced Pro Wire Tracer Kit

EC&M.
Product of the Year
2024 Category Winner

Built to Keep You Safe

The Fluke 2062 Advanced Pro Wire Tracer accurately and safely troubleshoots energized and de-energized wires in residential, commercial, and industrial environments up to CAT IV 600 V. This CAT rating offers the highest protection available on any wire tracer. It's designed to protect you from the most dangerous levels of transient overvoltage, spikes up to 8,000 V, that can occur in industrial and utility environments. This is especially important for scenarios you may encounter in environments like industrial plants, factories, and hospitals where critical equipment cannot be taken offline.

Smarter Tracing Saves Time

The patented Smart Sensor™, available only on the Fluke 2062, makes wire tracing faster and easier. It locates and displays energized wires within walls, floors, and ceilings on a high-resolution 3.5-inch TFT LCD color display. Embedded help screens on the display makes it easy to use, whether you're a novice or an expert. While the tip sensor provides an audible tone when locating wires, the Smart Sensor helps visualize and pinpoint the orientation of energized wires, eliminating guesswork.

Wire Tracing Customized for Your Application

Whether troubleshooting electrical wiring and equipment in residential homes, commercial buildings, or high-voltage utility plants, the Fluke 2062 can find breaks or opens and shorts. Its different modes and functions give you the flexibility to troubleshoot a wide range of electrical wiring and circuitry problems you may encounter on the job.

Four Receiver Tracing Modes

The 2062-R Receiver detects the signal in wires and cables using two methods: passive tracing without the transmitter for non-contact voltage detection and active tracing with the transmitter for all other modes. The receiver's tip sensor can trace wires in corners, tight spaces, and junction boxes.

- "Smart Sensor" mode for energized wire detection and visualization on the large color LCD
- "Tip Sensor" mode for more precise detection of a wire
- "Breaker" mode for easy breaker and fuse identification based on the highest recorded signal detected from the transmitter
- "Non-Contact Voltage Detection" mode to trace energized wires without the use of the transmitter

Three Transmitter Power Modes

The 2000-T Transmitter works on energized and de-energized circuits up to CAT IV 600 V and features high, low, and loop modes. These modes change the strength of the induced signal and can help provide more accurate results, depending on the circuit you're tracing.

- "High" mode for normal energized and de-energized circuits
- "Low" mode for precision tracing with a low signal to reduce coupling to nearby wires and metal objects
- "Loop" mode for closed loop de-energized circuits

Two Transmitter Output Frequencies

The 2000-T automatically senses whether the system is energized or de-energized and selects a 6 kHz or 33 kHz output frequency.

Eight Receiver Sensitivity Levels

More sensitivity levels mean more flexibility and accuracy when tracing.

Complete Kit

The Fluke 2062 Advanced Pro Wire Tracer Kit conveniently comes with everything required to start tracing wires and circuits. The accessory kit includes test leads, test probes, blade and round outlet adapters, and alligator clips to connect the transmitter to electrical systems. Connecting the transmitter to a bare conductor with the included alligator clips and test leads will always provide the most accurate results. However, in situations where a direct connection to a bare conductor is not available, the included i400 Current Clamp can be used with the “Loop” mode to induce a boosted 6 kHz signal through the insulation. The kit also includes a magnetic hanger strap, batteries, and a hard carrying case.

Specifications: Fluke 2062 Advanced Pro Wire Tracer Kit

Ordering information



2062

Includes:

- Fluke 2062R Advanced Pro Wire Tracer Receiver with Smart Sensor™
- Fluke 2000T Advanced Wire Tracer Transmitter
- i400 AC Current Clamp
- Fluke 2000ACC Test Lead Accessory Kit for 2052/2062
- Smart strap magnetic hanger
- Premium hard carrying case
- Batteries
- Quick reference guide

Optional accessories

Fluke i400 AC Current Clamp

Description

Fluke i400 AC current clamps extend the use of digital multimeters. Get a single range 400 A AC clamp in a compact shape.

Fluke TPAK ToolPak™ Magnetic Meter Hanger

Powerful magnetic strap for safe, hands free measurements.

CXT1000 Extreme Hard Case

The CXT1000 is a rugged hard case that allows you to configure the diced foam interior to store, protect, and carry your all your Fluke test tools and accessories.

Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Canada (800) 36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com

©2025 Fluke Corporation.
Specifications subject to change without notice.
07/2025

**Modification of this document is not permitted
without written permission from Fluke
Corporation.**