

Fluke 110 True-rms Digital Multimeter



Key features

- True-rms ac voltage for accurate measurements on non-linear signals
- Resistance and continuity
- Large white LED backlight to work in poorly lit areas

Product overview: Fluke 110 True-rms Digital Multimeter

Compact true-rms meter for accurate electrical installation and troubleshooting

The Fluke 110 is a versatile multimeter for electrical measurements and troubleshooting. Trusted by residential and commercial electricians for troubleshooting and maintenance. The 110 is for professional use, where true-rms accuracy is needed.

Key product capabilities

- True-rms ac voltage for accurate measurements on non-linear signals
- Large white LED backlight to work in poorly lit areas
- Resistance and continuity
- Min/Max/Average to record signal fluctuations
- CAT III 600 V safety rated

Specifications: Fluke 110 True-rms Digital Multimeter

Accuracy is specified for 1 year after calibration, at operating temperatures of 18 °C to 28 °C, with relative humidity at 0 % to 90 %. The accuracy specifications take the form of: \pm ([% of Reading] + [Counts])

General specifications			
Maximum voltage (between any terminal and earth ground)	600V		
Safety	IEC 61010-1, Pollution degree 2 IEC 61010-2-033, CAT III 600 V		
Display	Digital: 6,000 counts, updates 4/sec		
Bar graph	33 segments, updates 32/sec		
Temperature Operating Storage	-10 °C to + 50 °C -40 °C to + 60 °C		
Battery	9 volt Alkaline, IEC 6LR61		
Battery life	400 hours typical, without backlight		
Accuracy			
Measurement	Range	Resolution	Accuracy \pm ([% of reading] + [counts])
DC millivolts	600.0 mV	0.1 mV	0.5 % + 2
DC volts	6.000 V 60.00 V 600.0 V	0.001 V 0.01 V 0.1 V	0.5 % + 2
Accuracy			
Measurement	Range	Resolution	Accuracy \pm ([% of reading] + [counts])
AC millivolts ¹ true-rms	600.0 mV	0.1 mV	1.0 % + 3 (dc, 45 Hz to 500 Hz) 2.0 % + 3 (500 Hz to 1 kHz)
AC volts ¹ true-rms	6.000 V 60.00 V 600.0 V	0.001 V 0.01 V 0.1 V	1.0 % + 3 (dc, 45 Hz to 500 Hz) 2.0 % + 3 (500 Hz to 1 kHz)
Continuity	600 Ω	1 Ω	Beeper on < 20 Ω , off > 250 Ω ; detects opens or shorts of 500 μ s or longer.
Ohms	600.0 Ω	0.1 Ω	0.9 % + 2
	6.000 k Ω 60.00 k Ω 600.0 k Ω 6.000 M Ω	0.001 k Ω 0.01 k Ω 0.1 k Ω 0.001 M Ω	0.9 % + 1
	40.00 M Ω	0.01 M Ω	5 % + 2

¹All ac voltage ranges are specified from 1 % to 100% of range. Because inputs below 1 % of range are not specified, it is normal for this and other true-rms meters to display non-zero readings when the test leads are disconnected from a circuit or are shorted together. For volts, crest factor of \leq 3 at 4000 counts, decreasing linearly to 1.5 at full scale. AC volts is ac-coupled.

Ordering information



Fluke 110 True-rms DMM

Includes:

- Fluke 110 True-RMS Multimeter
- TL75 Hard Point™ Test Lead Set with protective caps
- 9 V battery (installed)

Optional accessories

Description

Fluke TPAK ToolPak™ Magnetic Meter Hanger	Powerful magnetic strap for safe, hands free measurements.
Fluke TL175 TwistGuard™ Test Leads	Simply twist to change the exposed probe tip length.
Fluke C25 Large Soft Case for DMMs	Fits most mid-sized multimeters, process and temperature meters.
Fluke i1010 AC/DC Current Clamp	Highly reliable, measures 1 A to 1000 A and provides accurate current reading without breaking the circuit. Buy Online Now.

