

Fluke 1587 MDT: Advanced Motor and Drive Troubleshooting Kit



Key features

Includes a Fluke 1587 Insulation Multimeter, Fluke i400 Current Clamp, and a Fluke 9040 Phase Rotation Indicator.

- With the Fluke 1587, perform insulation tests, plus a wide-range of DMM tasks with confidence and ease.
- Use the Fluke i400 with your Fluke 1587 to accurately measure AC current without breaking the circuit.
- Check the rotation of three-phase motors easily and safely with the Fluke 9040.

Product overview: Fluke 1587 MDT: Advanced Motor and Drive Troubleshooting Kit

The products in this kit have been specifically selected for both troubleshooting and preventative maintenance applications.

Establishing preventative maintenance programs are becoming critical to maintaining the uptime of electrical equipment and can significantly reduce both planned and unplanned downtime. Unplanned downtime costs are difficult to calculate, but often significant. For some industries, it can represent 1% - 3% of revenue (potentially 30% - 40% of profits) annually.

Includes a Fluke 1587 Insulation Multimeter, Fluke i400 Current Clamp, and a Fluke 9040 Phase Rotation Indicator.

Specifications: Fluke 1587 MDT: Advanced Motor and Drive Troubleshooting Kit

Includes a Fluke 1587 Insulation Multimeter, Fluke i400 Current Clamp, and a Fluke 9040 Phase Rotation Indicator.

[Fluke 1587 Insulation Multimeter](#)

- Two products in one: Powerful [Insulation Tester](#) and Full-featured Multimeter
- Ideal for work on motors, cables, and switch gear
- Large display with backlight
- Filter for motor drive measurements
- Insulation test (0.01 MΩ to 2 GΩ)
- Insulation test voltages (50 V, 100 V, 250 V, 500 V, 1000 V) for many applications
- CAT III 1000 V /CAT IV 600 V overvoltage rating for added user protection
- 3 year warranty

[Complete specifications](#)

[Fluke i400 AC Current Clamp](#)

- Use with your Fluke 1587 to measure 1A AC to 400 A AC
- 1 mA/Amp output guarantees easy reading
- CAT III 1000 V / CAT IV 600 V overvoltage rating for added user protection
- Specially designed to offer maximum utility in a very compact shape
- Maximum conductor: Ø 32 mm
- 1 year warranty

[Complete specifications](#)

[Fluke 9040 Phase Rotation Indicator](#)

- Large display to easily determine field rotation and phase sequence
- Indication for all three phases
- CAT III 600 V overvoltage rating
- 2 year warranty

[Complete specifications](#)

Ordering information



Fluke 1587/MDT Kit

Fluke 1587/MDT Advanced Motor and Drive Troubleshooting Kit

Includes:

- Fluke 1587 Insulation Multimeter
 - Fluke i400 Current Clamp
 - Fluke 9040 Phase Rotation Indicator
-



Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Canada (800) 36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com

©2021 Fluke Corporation.
Specifications subject to change without notice.
12/2021

**Modification of this document is not permitted
without written permission from Fluke Corporation.**