

Fluke 2680 Series Data Acquisition Systems



Key features

- 20 to 120 universal analog inputs per chassis; systems to +2,000 channels
- Stand-alone data logger operation with the 2686A
- Large scalable LAN systems using the 2680A with 10BaseT/100BaseT
- Two types of Universal Input Modules: high-isolation precision modules or fast scan modules, with 16- to 18-bit resolution
- Throughput of more than 3,000 channels-per-second-per-chassis with 2680A-FAI modules
- Superior thermocouple measurement accuracy (J, K, R, S, T, N, I, U, C, B)
- 20 digital I/O and 8 form C, 1 Amp relay output modules for direct control of equipment
- Up to 300V input isolation, 1600V transient overvoltage protection (2680A-PAI)
- Universal input conditioning for any input, on any channel, in any combination (V dc, V ac, Ohms, frequency, RTD, thermocouple, thermistor or current)
- ATA flash memory card for stand-alone operation - from 16 MB to 1 GB (2686A only)
- Multiple power sources: 100 to 240 V and 9 V to 45 V dc
- Includes Fluke DAQ Software which: Controls all 2680 Series functions, provides real-time and historical and also communicates with and 2645A NetDAQ products

Product overview: Fluke 2680 Series Data Acquisition Systems

Standalone or networked precision multi-channel DAQ

The Fluke 2680 Series data acquisition systems combine the best of lab precision with the rugged flexibility required in rapidly changing industrial applications. Whether you choose the 2680A Data Acquisition System with high-speed 10/100BaseT Ethernet network support or the 2686A Data Logging System, you can seamlessly expand your system any time from 20 to more than 2,000 channels, just by adding modules and chassis.

Both models feature six slots in each chassis that you can fill with modules as needed to meet your application requirements. Five slots in each chassis are available for any combination of 2680 Series 20-channel analog input modules. The sixth slot is reserved for a 2680 Series digital I/O relay module to add control capabilities to your system. If you don't need the sixth slot for control, you can plug in an additional analog input module, increasing your channel count to 120 in a single chassis.

You can also link multiple 120-channel systems together seamlessly for the widest possible view of your data. And with TCP/IP connectivity you can connect to existing LANs to distribute information wherever it needs to go. Whether you need speed and throughput, isolated precision, or digital I/O and relays, the Fluke 2680 Series can scale up to thousands of channels to meet your needs.

The Fluke 2680 Series offers the choice of networked data acquisition, stand-alone data logging, or a combination of both. Choose from two basic chassis models:

2680A Data Acquisition System chassis

The Fluke 2680A Data Acquisition System is the choice for multi-channel applications requiring reliable Ethernet communications. It features a front-end style data acquisition system that communicates and distributes data anywhere you need it to go. The 10BaseT and 100BaseT communications interface makes it compatible with both older and newer network installations.

2686A Data Logging System chassis

The Fluke 2686A Data Logging System writes data to a memory card for easy retrieval and storage, making it ideal for remote locations and mobile or non-computer assisted data logging applications. The system comes with a 16 MB ATA memory card and supports ATA flash memory cards of up to 1 GB to provide the memory capacity you need. The 2686A is easily configured for stand-alone data logging operations by simply selecting a preset configuration from the memory card. It can also be used in networks in tandem with the 2680A to provide the extra data security of a memory card.

Scale your system to meet your needs

With the Fluke 2680A and the 2686A, you can seamlessly expand your system from 20 to more than 2,000 channels just by adding modules and chassis. Both models feature six slots in each chassis that you can fill with modules as needed to meet your application requirements. Five slots in each chassis are available for any combination of 20-channel analog input modules. The sixth slot is also available for a digital I/O relay module to add control capabilities to your system. If you don't need the sixth slot for control, you can plug in an additional analog input module, increasing your input channel count to 120 in one chassis.

You can also link multiple 120-channel systems together seamlessly for the widest possible view of your data. And, with TCP/IP connectivity, you can connect to existing LANs to distribute information wherever it needs to go.

Whether you need speed and throughput, isolated precision, or digital I/O and relays, the Fluke 2680 Series can scale up to thousands of channels to meet your needs. Buy just the modules you need in the combinations you need and expand your system as your requirements grow.

2680A-FAI: the speed to capture dynamic process changes

The Fluke 2680A-FAI (Fast Analog Input) is a perfect choice when you need a lot of information in a hurry and still need to maintain a high degree of accuracy for your measurements. The 2680A-FAI module provides chassis throughput rates of more than 3,000 channels-per-second. Specially manufactured field effect transistors (FETs) allow up to + 50 V input, and channel-to-channel isolation well above the 15 V industry norm, to give you more confidence in the integrity of your measurements.

2680A-PAI provides high precision and high isolation for the most demanding jobs

The Fluke 2680A-PAI (Precision Analog Input) 20-channel high-precision, high-isolation module serves the most demanding jobs where precision is paramount and isolation is critical. Some of the most notable applications for this module include temperature measurement in semiconductor and pharmaceutical manufacturing, as well as nuclear plant performance

monitoring. The 2680A-PAI module offers 300 V of isolation on two channels and 150 V on 18 channels, as well as 18-bit resolution and excellent thermocouple accuracy, all in a scalable system.

Both the 2680A-FAI and the 2680A-PAI modules support a wide range of inputs including dc volts, ac volts, RTD, Ohms, thermocouple, thermistor, dc current, ac current, and frequency. Other sensors and transducers, such as load cells, pressure sensors, and displacement sensors can be easily incorporated into your measurement system.

2680A-DIO: Digital I/O and relay outputs add control

For data acquisition systems that also require control functionality, the Fluke 2680A-DIO digital I/O and relay output module provides 20 digital I/O and eight hard-contact 1 Amp form-C relays. This equips each chassis to respond to a wide range of alarm or control situations. The 2680A-DIO also includes an up/down counter with preset start count capability, so you do not need to begin all counts at zero.

2680A-180: Universal Input Module requires no external signal conditioning

Fluke's patented Universal Input Module is a special connector that is included with Fluke data acquisition products, providing unparalleled thermocouple accuracy and compatibility with a broad range of diverse inputs. The signal conditioning built into Fluke data acquisition products enables you to easily measure just about any electrical or physical parameter without changing hardware or adding external signal conditioning. You can connect any combination of dc voltage, ac voltage, thermocouples, current, RTD, resistance (2- or 4-wire) or frequency measurement inputs directly to the Universal Input Module.

Fluke DAQ Software makes it easy to get the most out of your data

Each Fluke 2680A and 2686A comes with our powerful, highly flexible, yet easy-to-use Fluke DAQ Configuration Software. Fluke DAQ allows you to configure the 2680 Series for:

- Input type
- Alarms
- Math functions
- Totalizer function
- Digital I/O lines
- Scan speed
- Interval
- Trigger type

You can also use Fluke DAQ Software to set up data files, collect and chart data in real-time or historical mode, and manage PC card files. And you can use Fluke DAQ to collect data from your system the way you need to and distribute it where you want it. You can share data with others, anywhere on your LAN or anywhere around the world using Web servers.

Fluke DAQ Software also enables you to integrate Fluke NetDAQ® data acquisition products (2640A and 2645A) into your 2680 Series system, providing almost unlimited channels working together seamlessly.

[Download FlukeDAQ 4.0 demonstration software.](#)

Optional software extends system capabilities

Fluke 2680A-904: Trend Link software

Trend Link for the 2680 Series is a comprehensive and powerful trend plotting software package. The Trend Link software allows users to access, view, and analyze tremendous amounts of historical and real time data in a trending or chart recorder-like display. With Trend Link, you can zoom in on points of interest in your data, or zoom out to display a wide overview of long-term trends. It can calculate basic statistics such as the mean and standard deviation on individual trends. Trend Link can define, save and display multiple charts to view logged data in different ways or arrangements. Trend Link is also capable of exporting selected sections of the data for analysis or manipulation in other software.

Fluke has partnered with industrial software developer Indusoft to create additional tools to extend the power of your 2680 Series system. These optional software tools enable you to create HMIs and develop custom applications that interact with

other equipment and software packages.

Fluke 2680A-DEVSW: HMI development software

The optional 2680A-DEVSW Indusoft Web Studio development software is an object-oriented development program that works with Fluke DAQ software. This unique development software enables programmers and non-programmers to develop modern HMIs which open graphical windows to your application.

Fluke 2680A-OPC: Communicate with any application supporting OLE for Process Control

This OPC server software provides the configuration interface for the 2680 Series and also offers a common communication link to any software package that supports OPC. Create custom applications using 2680A-OPC software and just about any popular industrial software package such as Wonderware™, LabVIEW™ Test Point, or Indusoft Web Studio, as well as software from Canary Labs, Daisy Labs, and others. Open, non-proprietary OPC support enables you to use the software you choose or the software you create.

Fluke 2680A-DLL library: For developing or modifying applications

The 2680A DLL library provides the full DLL toolbox for application software developers who need to write original programs for the 2680 Series, using Visual C++, Visual Basic, and other languages.

Specifications: Fluke 2680 Series Data Acquisition Systems

Technical Specifications	
Channel capacity (2680A or 2686A)	20 to 120 channels per chassis (6 analog input modules of 20 channels each)
	One master alarm (open collector) per chassis
	Communications: 10BaseT/100BaseT, TCP/IP via RJ45 connector, Cat 5
Math functions	In addition to its analog and digital input channels, each system supports 60 computed channels. Calculations include: time & rate, addition, subtraction, multiplication, division, log, natural log, exponent, square root, absolute value, integer function and average.
Measurement speed (2680A-PAI)	Slow: 6 readings/second nominal
	Medium: 41 (50 Hz), 48 (60 Hz) readings/second nominal
	Fast: 143 readings/second for VAC nominal, 140 readings/second on 300 Ω range, 37 readings/second on 3 MΩ range)
Measurement speed (2680A-FAI)	Slow: 45 (50 Hz), 54 (60 Hz) readings/second nominal
	Medium: 200 readings/second nominal
	Fast: 1000 readings/second nominal (5 readings/second for VAC nominal, 370 readings/second on 300 Ω range, 44 readings/second on 3 MΩ range)
Analog to digital converter	2680A-PAI: 18 bit, multi-slope type
	2680A-FAI: 16 bit, multi-slope type
Common mode rejection	2680A-PAI: AC: > 120 dB (50/60 Hz, + 0.1 % max 1 kΩ source imbalance) DC: > 120 dB
	2680A-FAI: AC: > 100 dB (50/60 Hz, + 0.1 % max 1 kΩ source imbalance) DC: > 100 dB
Normal mode rejection	50 dB @ 50/60 Hz, ± 0.1 %

Common mode voltage maximum	2680A-PAI:	300 V DC or v AC rms (channels 1,11); 25% V dc or V ac rms (all other channels)
	2680A-FAI:	50 V dc or 30 V ac rms (all channels)
Totalizing input (2680A-DIO)	Pre-settable starting count up/down counter DC coupled, non-isolated, max + 30 V, min – 4 V	
	Max count:	4,292,967,295
	Minimum signal:	2 V pead
	Threshold:	1.4 V
	Rate:	0-5 kHz (debounce off)
	Hysteresis:	500 mV
	Input debouncing:	none or 1.66 ms
Digital Inputs/Outputs: 20 (2680A-DIO)	Threshold:	1.4 V
	Hysteresis:	500 mV
	Maximum input:	+30V, min –4 V; non-isolated Logical "zero" output:
	Logical "zero" output:	0.8 V max out = -1.0 mA (1 LSTTL load equivalent)
		1.8 V max out = -20 mA
		3.25 V max out = -50 mA
		Output voltage depends on external load
		3.8 V min out = 0.05 mA (1 LSTTL load equivalent)
Relays (2680A-DIO)	Quantity:	8
	Type:	form C; DPST
	Current:	1 amp, non-inductive
	Operation time:	75 ms
Alarm associations (2680A-DIO)	Each Digital I/O may be randomly assigned as a digital input, status output, or alarm output (associated with any input channel or channels)	
Trigger input	Minimum pulse:	5 μs
	Minimum latency:	100 ms
	Input "High":	2.0 V min, 7.0 V max
	Input "Low":	-0.6 V min, 0.8 V max non-isolated, contact closure and TTL compatible
Clock	Accurate to within 1 minute/month for 0 °C to 50 °C range	

General Specifications

Power, battery life	100 to 240 V ac, 50 or 60 Hz 100 VA max, or 9 to 45 V dc (50 W max – all slots filled + memory card installed) (if both sources are applied simultaneously, the greater of ac or dc is used) at 120 V ac the equivalent dc voltage ~14.5 V
----------------------------	--

Temperature, humidity (non-condensing)	>Operating:	-20 °C to 28 °C, < 90 % RH:
		28 °C to 40 °C, < 75 % RH;
		40 °C to 60 °C, < 50 % RH
	Storage:	-40 °C to 70 °C, 5 % to 95 % RH
Altitude	Operating:	2000 m
	Storage:	12,200 m
Standards	All inputs:	IEC Overvoltage rating Category II Product conforms to the following safety and emissions standards:
		EN50082-2
		EN55022-1
		EN550aa class A
		EN61000-4-2, 3, 4, 6, 8
		EN61326
		EN61010-1, CAT II CSA C22.2 No. 1010.1
Operating Temperature	-20 °C to 60 °C (-4 °F to +140 °F)	
Storage Temperature	-40 °C to 70 °C (-40 °F to +158 °F)	
Size	18.6" x 17 " x 9.3" (473 mm x 423 mm x 237 mm)	
Weight	2680A/2686A chassis only: 18.86 lbs (8.47 kg) 2680A-FAI: 1.74 lbs. (0.79 kg) 2680A-PAI: 2.66 lbs, (1.21 kg) 2680A-DIO: 1.75 lbs. (0.80 kg)	
Interfaces	Ethernet: conforms to IEEE 802.3 Ethernet standard, compatible with 100BaseT and 10BaseT standards, uses TCP/IP protocol RS-232C: for calibration only	
System Requirements	IBM compatible, Pentium II processor Microsoft Windows® NT/98/2000/XP 64 MB RAM 25% MB free hard disk space VGA or SVGA display, 100 % IBM compatible with 2 MB Video RAM (VRAM) CD-ROM drive Microsoft Internet Explorer 4.0 or later	

Ordering information



Fluke 2680A-FAI

Fluke 2680A-FAI Fast Analog Input Module

- 20 universal channels
- 50 V max isolation
- 16-bit resolution
- 1000 ch/sec scan rate
- Includes universal input module 2680A-180
- Statement of Calibration Practices

Fluke 2680A-PAI

Fluke 2680A-PAI Precision Analog Input Module

- 20 universal channels
- 300 V Max isolation
- 18-bit resolution
- 140 ch/sec scan rate
- Includes universal input module 2680A-180
- Statement of Calibration Practices

Fluke 2686A

Fluke 2686A Data Acquisition System

- Fluke DAQ Software
- Product manual on CD
- Alarm/Trigger/DC Power Connector
- 1 meter cross-over, Ethernet cable
- Line Cord
- Type T thermocouple
- 1 GB flash memory card

Fluke 2680A-DIO

Fluke 2680A-DIO Digital I/O and relay module (one per chassis)

-
- 20 digital input/outputs, 8 1-Amp contacts, 1 totalizer
 - Includes DIO connector module 2680A-102
-

Fluke 2680A

Fluke 2680A Data Acquisition System

-
- Fluke DAQ Software
 - Product manual on CD
 - Alarm/Trigger/DC Power Connector
 - 1 meter cross-over, Ethernet cable
 - Line Cord
 - Type T thermocouple
-



Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Canada (800) 36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com

©2021 Fluke Corporation.
Specifications subject to change without notice.
11/2021

**Modification of this document is not permitted
without written permission from Fluke Corporation.**