

TECHNICAL DATA

Fluke TiX660 Infrared Camera



Key features

- 640 x 480 infrared camera with large 5.6-inch high resolution LCD screen
- Provides temperature measurements from -40°C to +1200°C (-40°F to 2192°F)
- Offers a high temperature option for measurements up to 2000 °C (3632 °F)

Product overview: Fluke TiX660 Infrared Camera


The TiX660 includes all the features of the TiX640 plus LaserSharp® Auto Focus and a high temperature option. You can use the 32x on-camera digital zoom to get spectacular, detailed infrared images from a safe distance. In addition to LaserSharp Auto Focus you also get auto focus, manual, and EverSharp multifocal recording to save time while get consistently accurate images. And with the large 5.6 inch high resolution LCD screen you can see more detail in every image on the and get high measurement accuracy with 640 x 480 resolution.

To further enhance your ability to see details from long distances, the TiX660 provides 4x the on-camera pixels in Super Resolution mode to give you 1280 x 960 (1,228,800 pixels) images (in software). You can work from safer distances and inspect areas that you could not get close to any other way and still get spectacular, detailed infrared images.


For added versatility, the TiX660 is also compatible with seven optional field installable lenses (2x and 4x telephoto lenses, two wide angle lenses, three macro lenses) in addition to the standard lens.

Other useful features:

- Features 32x on-camera digital zoom to allow you to get close up shots from a safe distance
- Provides 4x the pixel data with SuperResolution to create a 1280 x 960 (1,228,800 pixels) image (in software)



The TiX640 gives you 32x on-camera digital zoom for spectacular, detailed infrared images from a safe distance.



R&D testing of material absorbency and moisture permeation.



8 optional lens for maximum versatility.

- Offers multiple image transfer protocols
- Features the most advanced focus options available for consistently in focus images: Auto focus, manual, and EverSharp multifocal recording all on one camera
- Features LaserSharp® Auto Focus to produce consistently in-focus images for more accurate temperature measurements
- Includes a built-in laser distance meter that calculates the distance to your designated target up to 30 meters (100 feet)
- Provides the sharpest ever IR-Fusion® images with an 8 MP visible light camera
- Offers versatile viewing options for in-field viewing of images with viewfinder for outdoor use.
- Enables quick and easy in-field analysis with IR-Fusion® blending technology and advanced touchscreen functions including continuous level and span adjustment and filter mode for improved thermal sensitivity
- Features light and ergonomic handling with neck and hand strap for all day use
- Offers user defined programmable buttons to personalize for quick access to most used features.
- Allows sub-windowing to 240 Hz frame rate for advanced applications (add-on option)

Specifications: Fluke TiX660 Infrared Camera

Image Quality	
I FOV (spatial resolution)	0.8 mRad
Image resolution (pixel)	640 x 480 (307,200 pixels)
	1280 x 960 (1,228,800 pixels) (SuperResolution mode)
Frame rate (@ max. image resolution)	60 and 9 Hz
SuperResolution & Dynamic SuperResolutin (resolution enhancement)	Yes, MicroScan technology quadruples IR measurement pixels
Subwindowing modes available - subwindowing options are not available on 9 Hz models: (add on at time of order)	Option 1: 384 x 288 (120 fps) Option 2: 640 x 120 (240 fps)
Field of View (FOV) w/standard 30mm lens	30.9° x 23.1°
Thermal sensitivity (NETD)	≤ 0.03 °C at 30 °C target temp (30 mK)
Spectral range	7.5 μm to 14 μm
Wireless Connectivity	
Fluke Connect® compatible	No
IR-Fusion® Technology	
AutoBlend™ mode	Yes
Viewing modes	Picture-in-picture, continuous blending, color alarms (above and below user defined temperatures)

Focus System	
LaserSharp® Auto Focus	Yes
Auto focus	Yes
Manual focus	Yes, with the touch of a finger for tighter views
EverSharp multifocal recording	Yes, Multifocal recording captures images from different focal distances and combines them into one image displaying each object sharply for the best image quality
Temperature Measurement	
Range	-40 °C to +1200 °C (-40 °F to 2192 °F), High temperature option - request at time of order: up to 2000 °C (3632 °F)
Accuracy	± 1.5 °C or ± 1.5 %
Correction functions	LDC™ - Laser rangefinder based distance correction, emissivity (manual or material table)
	Transmissivity, ambient temperature, humidity (option)
Data Storage and Image Capture	
Image/video storage	SDHC memory card
Interfaces for image/data transfer	Supported in camera data ports: Image transfer: SD card, USB 2.0, video output DVI-D (HDMI). GigE vision and RS232 available in 2015
	SmartView® software: SD card. USB 2.0, GigE Vision and RS232 available in 2015
General Specifications	
Laser pointer	Yes, laser class: 2
Laser distance meter	Accuracy: ± 1.5 mm Range: 70 m (230 ft) Wavelength: 635 nm (red) Laser class: 2
Display	Extra-large 5.6" color TFT display, 1280 × 800 pixel resolution, Suitable for daylight operation
Geo-localization	Built-in GPS for geo-referencing
Digital visible light camera	Up to 8 megapixel resolution for image and video recording
Digital zoom	Up to 32x digital zoom
Text annotation	Yes
Voice annotation	Yes
Audio	Integrated microphone and loudspeaker for voice annotations
A/D conversion	16 bit
Power supply	External: 12 VDC ... 24 VDC Battery: Standard Li-Ion video camera battery

Replaceable Smart Batteries with LED level indicator	Two
Operating temperature	-25 °C to +55 °C (-13 °F to 131 °F)
Storing temperature	-40 °C to +70 °C (-40 °F to 158 °F)
Humidity	Relative humidity 10 % to 95 %, non-condensing
Shock	Operational: 25G, IEC 68-2-29
Vibration	Operational: 2G, IEC 68-2-6
Protection class	IP54
Ergonomics	Camcorder w/ handle
Viewfinder	Tiltable LCoS color viewfinder display, 800 × 600 pixel resolution
Dimensions (with standard 1.0/30 mm lens)	210 × 125 × 155 mm (8.25 x 4.9 x 6.1 in)
Weight (with standard 1.0/30 mm lens)	1.95 kg (4.3 lb)
Measurement functions (selection)	Multiple measurement spots & Regions of Interest (ROIs), hot/cold spot detection, isotherms, profiles, differences
Automatic functions (selection)	Focus, image, level, range, NUC, lens recognition, image optimization, alarm sequence
SmartView® software	Yes
Supported languages	Czech, Dutch, English, Finnish, French, German, Hungarian, Italian, Japanese, Korean, Polish, Portuguese, Russian, Simplified Chinese, Spanish, Swedish, Traditional Chinese and Turkish.
Warranty	2 years

Ordering information



FLK-TiX660 60 Hz

Fluke TiX660 Infrared Camera 60 Hz (640x480)

Includes:

- Two rechargeable batteries
- Battery charger and adapter
- AC adapter
- SD card reader
- FC SD card for Fluke Connect™ (not available in all countries)
- Protective lens cap
- Hand and neck straps
- Carrying case
- Warranty card and safety instructions
- Calibration certificate
- Printed manuals in English and Simplified Chinese

FLK-TiX660 9 Hz

Fluke TiX660 Infrared Camera 9 Hz (640x480)

Includes:

- Two rechargeable batteries
- Battery charger and adapter
- AC adapter
- SD card reader
- FC SD card for Fluke Connect™ (not available in all countries)
- Protective lens cap
- Hand and neck straps
- Carrying case
- Warranty card and safety instructions
- Calibration certificate
- Printed manuals in English and Simplified Chinese

Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Canada (800) 36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com

©2021 Fluke Corporation.
Specifications subject to change without notice.
12/2021

**Modification of this document is not permitted
without written permission from Fluke Corporation.**