

Fluke 700BCA Bar Code Adapter



Product overview: Fluke 700BCA Bar Code Adapter

Description: Shielded four conductor cable terminated with a 9-socket D-subminiature connector and a 9-pin D-subminiature connector.

Application: Provides interconnection and pin translation between a Fluke 743 Documenting Process Calibrator and a Hewlett Packard HBSW-8200 Bar Code Wand.

Specifications: Fluke 700BCA Bar Code Adapter

Mechanical and General Specifications	
Size	Overall length approximately 15 cm
Warranty	One year
Material	Black PVC cable and housings, tin plated shells, gold plated copper contacts

Ordering information



Fluke 700BCA

Bar Code Adapter

-
- Interface cable
 - Calibrator to bar code wand
 - Instruction sheet in English, French, German, Italian, and Spanish.
-

Fluke. *Keeping your world up and running.®*

Fluke Corporation

PO Box 9090, Everett, WA 98206 U.S.A.

Representative office of Fluke South East Asia Pte Ltd

C/O Danaher Vietnam
Green Power Tower, 11th Floor Unit 2
35 Ton Duch Thang Street, District 1
Ho Chi Minh City
Vietnam

Tel: +84-8-2220-5371 (ext 103)

Email: info.asean@fluke.com

www.fluke.com/vn-vi

©2021 Fluke Corporation. Specifications subject to change without notice.

11/2021

For more information call:

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa

+31 (0)40 267 5100

In Canada (905) 890-7600

From other countries +1 (425) 446-5500

Modification of this document is not permitted without written permission from Fluke Corporation.