

Fluke C150 Soft Carrying Case



Key features

- Zippered carrying case with belt loop
- Inner pocket for accessory storage
- Compatible with many Fluke products (see below)

Product overview: Fluke C150 Soft Carrying Case

Organize your Fluke tools and accessories with the C150 Soft Carrying Case featuring a deep zippered case. Inside is an additional pocket to store test leads or small accessories. The exterior is made with a durable, high-quality polyester. The C150 also includes a belt loop so you can always easily grab, go, and keep your tools with you. The case is also compatible with a variety of Fluke tools and clamp meters, including:

- [Fluke 325](#)
- [Fluke 376 FC](#)
- [Fluke 323](#)
- [Fluke 375 FC](#)
- [Fluke T5-1000](#)
- [Fluke 9040](#)

Specifications: Fluke C150 Soft Carrying Case

Dimensions:

298 x 114 x 56 mm

11.75 x 4.5 x 2.2 in

Ordering information



Fluke C150

Fluke. *Keeping your world up and running.®*

Fluke Corporation

PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa

+31 (0)40 267 5100

In Canada (905) 890-7600

From other countries +1 (425) 446-5500

Representative office of Fluke South East Asia Pte Ltd

C/O Danaher Vietnam

Green Power Tower, 11th Floor Unit 2

35 Ton Duch Thang Street, District 1

Ho Chi Minh City

Vietnam

Tel: +84-8-2220-5371 (ext 103)

Email: info.asean@fluke.com

www.fluke.com/vn-vi

©2021 Fluke Corporation. Specifications subject to change without notice.

12/2021

Modification of this document is not permitted without written permission from Fluke Corporation.