

TECHNICAL DATA

Fluke C700 Hard Carrying Case



Key features

- **Application:** Cutouts to hold one documenting process calibrator, one Fluke Pressure Module, one BC7210 Battery Charger, one spare BP7217 Battery Pack, and test leads
- **Material:**
 - Exterior: Blow-molded charcoal gray polyethylene with textured surface
 - Interior: Black, die-cut polyurethane foam
- **Handle:** Molded polyethylene
- **Latches:** Zinc-plated steel
- **Dimensions:** 47 x 40 x 14 cm
- **Weight:** 900 g
- **One year warranty**

Product overview: Fluke C700 Hard Carrying Case

Hard carrying case with custom-cut foam liner

Ordering information

**Fluke C700**

Fluke C700 Hard Carrying Case

Fluke. *Keeping your world up and running.®*

Fluke Corporation

PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa

+31 (0)40 267 5100

In Canada (905) 890-7600

From other countries +1 (425) 446-5500

Representative office of Fluke South East Asia Pte Ltd

C/O Danaher Vietnam

Green Power Tower, 11th Floor Unit 2

35 Ton Duch Thang Street, District 1

Ho Chi Minh City

Vietnam

Tel: +84-8-2220-5371 (ext 103)

Email: info.asean@fluke.com

www.fluke.com/vn-vi

©2021 Fluke Corporation. Specifications subject to change without notice.

12/2021

Modification of this document is not permitted without written permission from Fluke Corporation.