

## Fluke EI-1623 Selective/Stakeless Clamp Set



### Product overview: Fluke EI-1623 Selective/Stakeless Clamp Set

The Selective/Stakeless clamp set is used along with the Fluke 1623-2 and 1625-2 to perform Selective and Stakeless testing. Selective testing means using one clamp along with earth ground stakes to provide earth ground loop resistance values for one earth ground electrode. Stakeless testing uses both clamps provided to perform earth ground loop resistance measurement without stakes. Both tests have the advantage of providing measurements with no disconnection from the grounding system! Safer and quicker. Already included in the Fluke 1623-2 and 1625-2 kits. Both clamps have a 50.8 mm (2-inch) inner diameter.

## Ordering information



### **Fluke EI-1623**

Fluke EI-1623 Selective/Stakeless Clamp Set

---

**Fluke.** *Keeping your world up and running.®*

**Fluke Corporation**

PO Box 9090, Everett, WA 98206 U.S.A.

**For more information call:**

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa

+31 (0)40 267 5100

In Canada (905) 890-7600

From other countries +1 (425) 446-5500

**Representative office of Fluke South East Asia Pte Ltd**

C/O Danaher Vietnam

Green Power Tower, 11th Floor Unit 2

35 Ton Duch Thang Street, District 1

Ho Chi Minh City

Vietnam

Tel: +84-8-2220-5371 (ext 103)

Email: [info.asean@fluke.com](mailto:info.asean@fluke.com)

[www.fluke.com/vn-vi](http://www.fluke.com/vn-vi)

©2021 Fluke Corporation. Specifications subject to change without notice.

12/2021

**Modification of this document is not permitted without written permission from Fluke Corporation.**