

TECHNICAL DATA

## Fluke i1010-KIT AC/DC Current Clamp and Carry Case Kit



### Product overview: Fluke i1010-KIT AC/DC Current Clamp and Carry Case Kit

Special value kit for electrical professional who is looking to add on DC and AC current measurement capabilities to their DMM. Includes a roomy carry case to hold and protect your meter and current clamp, plus extra storage for your test leads, probes and manuals.

## Ordering information



### Fluke i1010 Kit

- i1010 1-600A AC rms, 1-1000A DC Current Clamp
- Zippered vinyl carry case with moveable divider

**Fluke.** *Keeping your world up and running.®*

**Fluke Corporation**

PO Box 9090, Everett, WA 98206 U.S.A.

**For more information call:**

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa

+31 (0)40 267 5100

In Canada (905) 890-7600

From other countries +1 (425) 446-5500

**Representative office of Fluke South East Asia Pte Ltd**

C/O Danaher Vietnam

Green Power Tower, 11th Floor Unit 2

35 Ton Duch Thang Street, District 1

Ho Chi Minh City

Vietnam

Tel: +84-8-2220-5371 (ext 103)

Email: [info.asean@fluke.com](mailto:info.asean@fluke.com)

[www.fluke.com/vn-vi](http://www.fluke.com/vn-vi)

©2021 Fluke Corporation. Specifications subject to change without notice.

12/2021

**Modification of this document is not permitted without written permission from Fluke Corporation.**