

TECHNICAL DATA

Fluke i1730-flex3000/3pk iFlex® Current Clamps



Product overview: Fluke i1730-flex3000/3pk iFlex® Current Clamps

The Fluke 1730 Energy Logger 24 inch iFlex® flexible current probes expand the measurement range of the Fluke 1730 to 3000 A ac while providing the ultimate measurement flexibility. The iFlex® probes connect directly to the energy logger, displaying current measurements without error prone scaling factors. The 1.8 m (6 ft) cord allows separation between the measurement location and the energy logger making it easier to view the display. Fluke 1730 Energy Logger iFlex® cables are available in 12, 24, and 36 inch.

Ordering information



Fluke i1730-flex3000/3pk

A 24 inch, 3 pack Current Clamps

-
- 3000A 24 inch, 3 pack iFlex® Current Clamps
-

Fluke. *Keeping your world up and running.®*

Fluke Corporation

PO Box 9090, Everett, WA 98206 U.S.A.

Representative office of Fluke South East Asia Pte Ltd

C/O Danaher Vietnam
Green Power Tower, 11th Floor Unit 2
35 Ton Duch Thang Street, District 1
Ho Chi Minh City
Vietnam

Tel: +84-8-2220-5371 (ext 103)

Email: info.asean@fluke.com

www.fluke.com/vn-vi

©2021 Fluke Corporation. Specifications subject to change without notice.
12/2021

For more information call:

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa

+31 (0)40 267 5100

In Canada (905) 890-7600

From other countries +1 (425) 446-5500

Modification of this document is not permitted without written permission from Fluke Corporation.