

TECHNICAL DATA

## Fluke i17XX-flex3000 iFlex® Current Clamp



### Product overview: Fluke i17XX-flex3000 iFlex® Current Clamp

The Fluke 17XX 24 inch iFlex® flexible current probes expand the measurement range of the Fluke 17XX Energy or Power Logger to 3000A AC while providing the ultimate measurement flexibility. The iFlex® probes connect directly to the logger, displaying current measurements without error prone scaling factors. The 1.8 m (6 ft) cord allows separation between the measurement location and the logger making it easier to view the display. Fluke 17XX iFlex® cables are available in 12, 24, and 36 inch.

## Ordering information



### **i17XX-flex3000**

3000A 24 inch iFlex® Current Clamps

---

**Fluke.** *Keeping your world up and running.®*

**Fluke Corporation**

PO Box 9090, Everett, WA 98206 U.S.A.

**Representative office of Fluke South East Asia Pte Ltd**

C/O Danaher Vietnam  
Green Power Tower, 11th Floor Unit 2  
35 Ton Duch Thang Street, District 1  
Ho Chi Minh City  
Vietnam

Tel: +84-8-2220-5371 (ext 103)

Email: [info.asean@fluke.com](mailto:info.asean@fluke.com)

[www.fluke.com/vn-vi](http://www.fluke.com/vn-vi)

©2021 Fluke Corporation. Specifications subject to change without notice.  
12/2021

**For more information call:**

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa

+31 (0)40 267 5100

In Canada (905) 890-7600

From other countries +1 (425) 446-5500

**Modification of this document is not permitted without written permission from Fluke Corporation.**