

TECHNICAL DATA


Fluke i17XX-flex6000 iFlex® Current Clamp



Product overview: Fluke i17XX-flex6000 iFlex® Current Clamp

The Fluke 17XX 36 inch iFlex flexible current probes expand the measurement range of the Fluke 17XX Energy or Power Logger to 6000A AC while providing the ultimate measurement flexibility. The iFlex probes connect directly to the energy logger, displaying current measurements without error prone scaling factors. The 1.8 m (6 ft) cord allows separation between the measurement location and the energy logger making it easier to view the display. Fluke 17XX iFlex cables are available in 12, 24, and 36 inch.

Ordering information



i17XX-flex6000

6000A 36 inch iFlex® Current Clamps

Fluke. *Keeping your world up and running.®*

Fluke Corporation

PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa

+31 (0)40 267 5100

In Canada (905) 890-7600

From other countries +1 (425) 446-5500

Representative office of Fluke South East Asia Pte Ltd

C/O Danaher Vietnam

Green Power Tower, 11th Floor Unit 2

35 Ton Duch Thang Street, District 1

Ho Chi Minh City

Vietnam

Tel: +84-8-2220-5371 (ext 103)

Email: info.asean@fluke.com

www.fluke.com/vn-vi

©2021 Fluke Corporation. Specifications subject to change without notice.

12/2021

Modification of this document is not permitted without written permission from Fluke Corporation.