

Fluke i3000 Flex AC Current Clamp, 4 Pack



Key features

- Three ranges
 - 30 A
 - 300 A
 - 3000 A, 1, 10 or 100 mV/A output
- Ideal for current measurement on thick and hard to reach conductors without breaking the circuit
- Maximum conductor diameter 178 mm (7 in)
- CAT III 600 V safety rating

Product overview: Fluke i3000 Flex AC Current Clamp, 4 Pack

The i3000s Flex is an AC current clamp utilizing the Rogowski principle. It can be used to measure currents up to 3000 A when used in conjunction with oscilloscopes, recorders or data loggers. The flexible and lightweight measuring head allows quick and easy installation in hard to reach areas.


Specifications: Fluke i3000 Flex AC Current Clamp, 4 Pack

Electrical Specifications	
Current ranges	30 A
	300 A
	3000 A
	AC rms

Output sensitivity (AC-coupled)	100 mV
	10 m
	1 mV per A
Load impedance	100 kΩ minimum
Accuracy	at +25°C
	±1% of range (45 Hz to 65 Hz)
Linearity	10% to 100% of range
	±0.2% of reading
Noise	8 mV AC rms (30 A)
	2 mV AC rms (300 A, 3000 A)
Frequency range	10 Hz to 50 kHz (-3 dB)
Phase error	< ±1° (45 Hz to 65 Hz)
	±10° (at 20 kHz)
Position sensitivity	with cable > 25 mm from the coupling
	±2% of range
External field	with cable > 200 mm from the head
	±1% of range
Power supply	2 x AA/MN 1500/LR6 Alkaline, 400 hours, low battery indicator
Temperature coefficient	±0.08% of reading per °C
Working voltage	see safety standards section
	600 V AC rms or DC
General Specifications	
Head circumference	610 mm (24in)
Head cable diameter	14.3 mm (0.56in)
Head bend radius	38.1 mm (1.5in)
Cable length (head to electronics)	2 m (6.56 ft)
Output connection	0.5 m cable terminated with safety BNC connector. Supplied with 4mm safety plug adapter
Operating temperature range	-20°C to +90°C (-4°F to 190°F) (head)
	-20°C to +85°C (-4°F to 185°F) (electronics)
Strong temperature range	-40°C to +105°C (-40°F to 221°F) (head)
	-20°C to +85°C (-4°F to 185°F) (electronics)
Operating humidity	15% to 85% (non-condensing)
Weight	180 g (0.396 lb) (head)
	190 g (0.419 lb) (electronics)

Safety standards	BS EN 61010-1: 2001
	BS EN 61010-2-032: 2002
	BS EN 61010-031: 2002
	600 Vrms, Category III, Pollution Degree 2
	Use of the probe on uninsulated conductors is limited to 600 V AC rms or DC and frequencies below 1 kHz
EMC standards	EN 61326: 1998 +A1, A2, and A3
Head cable length (double insulated)	610 mm or 914 mm, depending on model

Ordering information



Fluke i3000 Flex 4PK

Fluke. *Keeping your world up and running.®*

Fluke Corporation

PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa

+31 (0)40 267 5100

In Canada (905) 890-7600

From other countries +1 (425) 446-5500

Representative office of Fluke South East Asia Pte Ltd

C/O Danaher Vietnam

Green Power Tower, 11th Floor Unit 2

35 Ton Duch Thang Street, District 1

Ho Chi Minh City

Vietnam

Tel: +84-8-2220-5371 (ext 103)

Email: info.asean@fluke.com

www.fluke.com/vn-vi

©2021 Fluke Corporation. Specifications subject to change without notice.

12/2021

Modification of this document is not permitted without written permission from Fluke Corporation.