

TECHNICAL DATA

Fluke i40s-EL/3pk Clamp-on Current Transformers



Product overview: Fluke i40s-EL/3pk Clamp-on Current Transformers

The Fluke i40s-EL Current Clamp-on Transformer is used for low current measurement; suitable for making measurements up to 40A, and also measures accurately on 1A and 5A secondary current transformers. The i40s-EL jaw is capable of being clamped on current conductors up to 15mm in diameter.

Ordering information



Fluke i40s-EL/3pk

40A Clamp-on Current Transformer, 3 pack

Fluke. *Keeping your world up and running.®*

Fluke Corporation

PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa

+31 (0)40 267 5100

In Canada (905) 890-7600

From other countries +1 (425) 446-5500

Representative office of Fluke South East Asia Pte Ltd

C/O Danaher Vietnam

Green Power Tower, 11th Floor Unit 2

35 Ton Duch Thang Street, District 1

Ho Chi Minh City

Vietnam

Tel: +84-8-2220-5371 (ext 103)

Email: info.asean@fluke.com

www.fluke.com/vn-vi

©2021 Fluke Corporation. Specifications subject to change without notice.

12/2021

Modification of this document is not permitted without written permission from Fluke Corporation.