

Fluke i5S AC Current Clamp



Key features

- Low level current clamp measures up to 5 A AC
- Compact shape makes transporting and storing convenient; the clamp measures only 116 x 43 x 23 mm (4.6 x 1.7 x .9 in)
- Take accurate readings without breaking the circuit
- CAT III 600 V (For insulated conductors only)

Product overview: Fluke i5S AC Current Clamp

Expand the use of your Fluke 430 series power quality tool or ScopeMeter test tool with this 5 A AC current clamp, specially configured to provide good accuracy at low levels e.g. while taking measurements on secondary current transformers.

Specifications: Fluke i5S AC Current Clamp

Specifications	
Nominal current range	5 A
Continuous current range	10 mA to 6 A
Maximum Non-Destructive Current	70 A
Lowest measurable current	10 mA

Basic Accuracy		48 Hz to 65 Hz
	10 mA to 1 A	1% + 5 mA
	1 A to 5 A	1%
Useable frequency	40 Hz to 5 kHz	
Output level(s)	400 mV/A	
Input Load Impedance	> 1 M Ω in parallel with up to 47 pF	
Crest Factor	\leq 3, add 0.7% to accuracy	
Safety Specifications		
Safety	CAT III 600 V per IEC/EN61010-1, Pollution Degree 2	
Maximum voltage	600 V AC	
Mechanical and General Specifications		
Warranty	1 year	
Maximum conductor diameter	15 mm	
Output cable length	2.5 m	
BNC Adapter	Yes	
BNC to banana adapter included	No	

Ordering information



AC Current Clamp

Fluke. *Keeping your world up and running.®*

Fluke Corporation

PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa

+31 (0)40 267 5100

In Canada (905) 890-7600

From other countries +1 (425) 446-5500

Representative office of Fluke South East Asia Pte Ltd

C/O Danaher Vietnam

Green Power Tower, 11th Floor Unit 2

35 Ton Duch Thang Street, District 1

Ho Chi Minh City

Vietnam

Tel: +84-8-2220-5371 (ext 103)

Email: info.asean@fluke.com

www.fluke.com/vn-vi

©2021 Fluke Corporation. Specifications subject to change without notice.

12/2021

Modification of this document is not permitted without written permission from Fluke Corporation.