

Fluke TPS FLEX 24 Flexible Current Probe



Specifications: Fluke TPS FLEX 24 Flexible Current Probe

General Specifications	
Measuring range selectable per software	2 A to 200 A
	10 A to 1000 A
Peak current for sinusoidal currents	480 A
	2700 A
Intrinsic error	1%
Frequency range	45 Hz to 3.0 kHz
Operating voltage	600 V CAT IV
Phase error	0.5°
Jaw opening	61 cm length
	2 m cable
Errors in % of measuring range at 23°C ± 2 K; 74°F ± 2 K, for 48 to 65 Hz Phase angle error at nominal current I _{max} maximum current without time limit (for AC and DC shunts)	

Ordering information



Fluke TPS FLEX 24

Flexible Current Probe

Fluke. *Keeping your world up and running.®*

Fluke Corporation

PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa

+31 (0)40 267 5100

In Canada (905) 890-7600

From other countries +1 (425) 446-5500

Representative office of Fluke South East Asia Pte Ltd

C/O Danaher Vietnam

Green Power Tower, 11th Floor Unit 2

35 Ton Duch Thang Street, District 1

Ho Chi Minh City

Vietnam

Tel: +84-8-2220-5371 (ext 103)

Email: info.asean@fluke.com

www.fluke.com/vn-vi

©2021 Fluke Corporation. Specifications subject to change without notice.

12/2021

Modification of this document is not permitted without written permission from Fluke Corporation.