


TECHNICAL DATA

## Fluke 71X Hose Kit Accessory



### Product overview: Fluke 71X Hose Kit Accessory

**The Fluke 71X Hose Kit is compatible with the 717 and 718 calibrators 100 PSI and below.**

**Application:** Translucent accessory hoses allow the technician to easily identify if there is oil or other contaminants in the hose before they get into your calibrator.

**Included:** The kit contains three translucent hoses one meter long, easy to connect push fit connectors for both connection to the calibrator and the device under test, and one 1/8 to 1/4 NPT female-female adapter.

# Ordering information



## Fluke 71X

Hose Kit Accessory

---

**Fluke.** *Keeping your world up and running.®*

**Fluke Corporation**

PO Box 9090, Everett, WA 98206 U.S.A.

**For more information call:**

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa

+31 (0)40 267 5100

In Canada (905) 890-7600

From other countries +1 (425) 446-5500

**Representative office of Fluke South East Asia Pte Ltd**

C/O Danaher Vietnam

Green Power Tower, 11th Floor Unit 2

35 Ton Duch Thang Street, District 1

Ho Chi Minh City

Vietnam

Tel: +84-8-2220-5371 (ext 103)

Email: [info.asean@fluke.com](mailto:info.asean@fluke.com)

[www.fluke.com/vn-vi](http://www.fluke.com/vn-vi)

©2021 Fluke Corporation. Specifications subject to change without notice.

12/2021

**Modification of this document is not permitted without written permission from Fluke Corporation.**