

Fluke 80PK-11 Type-K Flexible Cuff Thermocouple Temperature Probe



Key features

- Designed for hands free measurement of HVAC temperature measuring applications
- Use multiple and leave in place for route based routine maintenance
- Use with any temperature-measuring instrument designed to accept Type-K thermocouples

Specifications: Fluke 80PK-11 Type-K Flexible Cuff Thermocouple Temperature Probe

Specifications	
Measurement range	-30°C to 150°C (-19.3°F to 302°F)
Accuracy	±1.5°C (±2.7°F)
Measurement time (time constant)	10 seconds
Maximum voltage	24 V AC rms or 60 V DC maximum for proper safe operation.
Maximum temperature	150°C (302°F)

Cable	Total length	1 m (40 in), 0.97 m (38 in) lead wire, 49.5 cm (19.5 in) fabric hook-and-loop fastener cuff
	Insulation material	Hytrel
	Width of attachment material	2.5 cm (1 in)
	Min usable pipe diameter	3.8 cm (1.5 in)
	Max. usable pipe diameter	14 cm (5.5 in)
Connector	Type	Yellow mini-thermocouple with 0.500 in pin
	Material	Hytrel 4774
	Maximum temperature	200°C (392°F)

Ordering information



Fluke 80PK 11

Fluke. *Keeping your world up and running.®*

Fluke Corporation

PO Box 9090, Everett, WA 98206 U.S.A.

Representative office of Fluke South East Asia Pte Ltd

C/O Danaher Vietnam
Green Power Tower, 11th Floor Unit 2
35 Ton Duch Thang Street, District 1
Ho Chi Minh City
Vietnam

Tel: +84-8-2220-5371 (ext 103)

Email: info.asean@fluke.com

www.fluke.com/vn-vi

©2021 Fluke Corporation. Specifications subject to change without notice.

11/2021

For more information call:

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa

+31 (0)40 267 5100

In Canada (905) 890-7600

From other countries +1 (425) 446-5500

Modification of this document is not permitted without written permission from Fluke Corporation.