

TECHNICAL DATA

Fluke 700 PMP Pressure Pump



Product overview: Fluke 700 PMP Pressure Pump

Description: The Fluke 700PMP is a hand-operated pressure pump to provide pressures up to 150 psi/1000 kPa. Output fitting is 1/8 FNPT.

Application: Linear stroke of 4 cm. Multi-turn vernier for fine adjustment of pressure.

Specifications: Fluke 700 PMP Pressure Pump

Mechanical and General Specifications	
Size	265 x 35 mm
Weight	340 g
Warranty	One year

Ordering information



Fluke 700PMP

PMP Pressure Pump

Instruction sheet

Fluke. *Keeping your world up and running.®*

Fluke Corporation

PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa

+31 (0)40 267 5100

In Canada (905) 890-7600

From other countries +1 (425) 446-5500

Representative office of Fluke South East Asia Pte Ltd

C/O Danaher Vietnam

Green Power Tower, 11th Floor Unit 2

35 Ton Duch Thang Street, District 1

Ho Chi Minh City

Vietnam

Tel: +84-8-2220-5371 (ext 103)

Email: info.asean@fluke.com

www.fluke.com/vn-vi

©2021 Fluke Corporation. Specifications subject to change without notice.

12/2021

Modification of this document is not permitted without written permission from Fluke Corporation.