

TECHNICAL DATA

# Fluke AC89 Heavy Duty Insulation Piercing Test Clip



## Key features

- Single probe pierces 0.25 to 1.5 mm insulated wire
- Extremely small piercing point allows for maximum integrity of insulation
- 30Vrms, 42.4Vpk, 60Vdc, 10A
- One year warranty

## Ordering information



**Fluke AC89**

---

**Fluke.** *Keeping your world up and running.®*

**Fluke Corporation**  
PO Box 9090, Everett, WA 98206 U.S.A.

**Representative office of Fluke South East Asia Pte Ltd**

C/O Danaher Vietnam  
Green Power Tower, 11th Floor Unit 2  
35 Ton Duch Thang Street, District 1  
Ho Chi Minh City  
Vietnam

Tel: +84-8-2220-5371 (ext 103)

Email: [info.asean@fluke.com](mailto:info.asean@fluke.com)

[www.fluke.com/vn-vi](http://www.fluke.com/vn-vi)

©2021 Fluke Corporation. Specifications subject to change without notice.  
12/2021

**For more information call:**

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa

+31 (0)40 267 5100

In Canada (905) 890-7600

From other countries +1 (425) 446-5500

**Modification of this document is not permitted without written permission from Fluke Corporation.**