

Fluke TL225 SureGrip™ Stray Voltage Adapter Test Lead Kit

Key features

The Fluke TL225 is the solution

- It makes sure the meter has a low input impedance that eliminates stray voltages
- On energized wires, the meter will indicate the real voltage
- On non-energized circuits the meter will read close to zero (even if there are stray voltages)
- It can be used with all modern meters with standard input spacing
- Rated CAT III 1000 V, CAT IV 600 V
- One year warranty

Product overview: Fluke TL225 SureGrip™ Stray Voltage Adapter Test Lead Kit

Electricians know that when you are measuring electrical installations there often appears to be a voltage, even if you know the wires are non energized. This is called stray or ghost voltages and is caused by the capacity between wires. Because of the very high impedance input of the meter, this stray voltage has nowhere to go which will lead to an incorrect reading on the meter.

The solution is to make sure there is a lower impedance across the input terminals of the meter. However, this is not as easy as it seems since it is vital that the safety of the electrician is not compromised.

Specifications: Fluke TL225 SureGrip™ Stray Voltage Adapter Test Lead Kit

Technical Specifications	
Operation temperature	-20°C to +55°C (-40°F to 131°F)
Altitude	2,000 meters operating
Humidity	90% at 0 to 35°C (32°F to 95°F) 70% at 35 to 55°C (95°F to 131°F)
Nominal resistance	3,000 Ω @ 25°C (77°F)



Ordering information

Fluke. *Keeping your world up and running.®*

Fluke Corporation

PO Box 9090, Everett, WA 98206 U.S.A.

Representative office of Fluke South East Asia Pte Ltd

C/O Danaher Vietnam
Green Power Tower, 11th Floor Unit 2
35 Ton Duch Thang Street, District 1
Ho Chi Minh City
Vietnam

Tel: +84-8-2220-5371 (ext 103)

Email: info.asean@fluke.com

www.fluke.com/vn-vi

©2021 Fluke Corporation. Specifications subject to change without notice.
12/2021

For more information call:

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa

+31 (0)40 267 5100

In Canada (905) 890-7600

From other countries +1 (425) 446-5500

Modification of this document is not permitted without written permission from Fluke Corporation.