


## TECHNICAL DATA

# Fluke 8.5 MM Scope with 1 M UV Videoscope Probe



## Key features

Optional 1 meter long, 8.5 millimeter Ultraviolet videoscope probe with forward view camera. Compatible with Fluke DS701 and Fluke DS703 FC Videoscopes. Supports all features of the Fluke Videoscopes except Up is Up™

## Product overview: Fluke 8.5 MM Scope with 1 M UV Videoscope Probe

Ideal for:

### Transportation

- Leaks with smoke and dye
- Structural damage of engine components
- Foreign object debris (FOD) inspection

### Oil and Gas

- Wear on pipes and hoses
- Structural damage in pipes and hoses

### Energy

- Quality control inspections
- Leak inspections

**Fluke.** *Keeping your world up and running.®*

**Fluke Corporation**

PO Box 9090, Everett, WA 98206 U.S.A.

**For more information call:**

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa

+31 (0)40 267 5100

In Canada (905) 890-7600

From other countries +1 (425) 446-5500

**Representative office of Fluke South East Asia Pte Ltd**

C/O Danaher Vietnam

Green Power Tower, 11th Floor Unit 2

35 Ton Duch Thang Street, District 1

Ho Chi Minh City

Vietnam

Tel: +84-8-2220-5371 (ext 103)

Email: [info.asean@fluke.com](mailto:info.asean@fluke.com)

[www.fluke.com/vn-vi](http://www.fluke.com/vn-vi)

©2021 Fluke Corporation. Specifications subject to change without notice.

12/2021

**Modification of this document is not permitted without written permission from Fluke Corporation.**