

# Smart Infrared 4x Telephoto Lens



## Product overview: Smart Infrared 4x Telephoto Lens

View your target magnified 4 times more than a standard lens while staying on the ground or a safe distance away. A 4x telephoto lens can help identify a potential issue in your equipment, even when your target is as tiny and distant as a failed splice on a high electrical line or an overheated refractory on a tall flare stack.

- Avoid the hassle of sending in your camera to calibrate with the lens - with smart lenses you can just attach the lens to any compatible camera and start taking images.
- This lens includes a patent-pending lens attachment system that holds the lens securely in place, reducing lens wobble.
- Made of 100% diamond-turned germanium with an engineered coating, the most efficient available material to transmit energy to the detector.

Compatible with TiX580, TiX501, Ti480 PRO, Ti401 PRO

## Specifications: Smart Infrared 4x Telephoto Lens

Description		
IFOV (spatial resolution)	Ti401 PRO / Ti480 PRO	0.17 mRad
	Ti300+	0.34 mRad
	TiX501 / TiX580	0.17 mRad
Field of view	6.0° H x 4.5° V	



Focus distance	1.5 m (approximately 5 ft)
----------------	----------------------------

## Ordering information



### **FLK-LENS/4XTELE2**

For use with the TiX580, TiX501, Ti480 PRO, Ti401 PRO Infrared Cameras.

**Fluke.** *Keeping your world up and running.®*

**Fluke Corporation**

PO Box 9090, Everett, WA 98206 U.S.A.

**For more information call:**

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa

+31 (0)40 267 5100

In Canada (905) 890-7600

From other countries +1 (425) 446-5500

**Representative office of Fluke South East Asia Pte Ltd**

C/O Danaher Vietnam

Green Power Tower, 11th Floor Unit 2

35 Ton Duch Thang Street, District 1

Ho Chi Minh City

Vietnam

Tel: +84-8-2220-5371 (ext 103)

Email: [info.asean@fluke.com](mailto:info.asean@fluke.com)

[www.fluke.com/vn-vi](http://www.fluke.com/vn-vi)

©2021 Fluke Corporation. Specifications subject to change without notice.

11/2021

**Modification of this document is not permitted without written permission from Fluke Corporation.**