

TECHNICAL DATA

Fluke Telephoto Infrared Lens



Key features

Field-of-View (FOV) is 8.6 ° x 6.5 °

Product overview: Fluke Telephoto Infrared Lens

Optional, field swappable, telephoto thermal lens allows the user to see and measure the temperature of objects at greater distances, or smaller objects at normal distances.

Ordering information



Fluke Lens/Tele1

Fluke Telephoto Infrared Lens

For use with: Ti32 and TiR32

Fluke. *Keeping your world up and running.®*

Fluke Corporation

PO Box 9090, Everett, WA 98206 U.S.A.

Representative office of Fluke South East Asia Pte Ltd

C/O Danaher Vietnam
Green Power Tower, 11th Floor Unit 2
35 Ton Duch Thang Street, District 1
Ho Chi Minh City
Vietnam

Tel: +84-8-2220-5371 (ext 103)

Email: info.asean@fluke.com

www.fluke.com/vn-vi

©2021 Fluke Corporation. Specifications subject to change without notice.
11/2021

For more information call:

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa

+31 (0)40 267 5100

In Canada (905) 890-7600

From other countries +1 (425) 446-5500

Modification of this document is not permitted without written permission from Fluke Corporation.