

Fluke 1750/B Three-Phase Basic Power Quality Recorder



Key features

- **Power quality that meets the standard** All measurements comply with IEC61000-4-30 standards for correct evaluation of all measured values including voltage, current, power, harmonics, flicker etc.
- **Quick and reliable configuration** A tablet computer provides a window into what the instrument is recording, enabling quick and reliable configuration even in awkward test locations
- **Threshold-free set up** Apply thresholds after data is collected with Fluke Power Analyze Software – no need to worry about missed information due to incorrect setups
- **Captures everything** Cross-channel and current triggering capture every measurement, on every channel, every time
- **Intuitive PC software** Easily analyze data and generate reports with automated EN50160 reporting and compliance
- **Reporting has never been easier** Auto Report creates either standard reports or customized reports with the minimum effort or hassle. Export reports to almost any format including RTF (Rich Text Format) for editing in Microsoft Word.
- **Plug and play** Set up in minutes with self-identifying current probes and single-lead voltage connections
- **No need to reconnect wires** Swap channels internally with the wireless PDA or PC when connections are not correct
- **Measure every parameter** Voltage and current on three phases, neutral, and ground
- **5 MHz, 8000 Vpk waveform capture** Get a detailed picture of even the shortest events
- **Quickly retrieve data** With included SD memory card or via the 100 BaseT high-speed Ethernet connection. SD card includes automatic download to SD when no other connection is made to the instrument

Product overview: Fluke 1750/B Three-Phase Basic Power Quality

Recorder

Record every power quality parameter, every cycle, all the time

Setting up a power quality analyzer to capture detailed power quality data has never been easier than it is with the Fluke 1750. The only things you need to know are the system voltage, frequency and the power configuration (delta or wye). The analyzer then captures the most important data for up to 30 days without losing the most important details. These power meters automatically record every power quality parameter and event, on every cycle – all the time. Once the data is captured download via Ethernet or directly to 2GB SD card (without the need of any other device). The Fluke 1750 features a wireless front panel for viewing measurements, data and setting up, implemented via a tablet computer using Bluetooth communication.

Applications

- Long-term analysis: Uncover hard-to-find or intermittent issues; monitor critical equipment, capturing power quality events to correlate with equipment malfunction
- Power quality surveys: Quantify power quality throughout a facility, documenting results with professional reports
- Quality of service compliance: Validate incoming power quality at the service entrance
- Equipment Installation/Commissioning: Benchmark: power system prior to install to insure quality of service
 - **Long-Term Analysis** – Uncover hard-to-find or intermittent issues.
 - **Load Studies** – Verify the available electrical system capacity before adding loads.

Specifications: Fluke 1750/B Three-Phase Basic Power Quality Recorder

Technical Specifications		
Power quality measurement standards	Conformance	IEC 61999-1-4 Class 1, IEC 61000-4-30 Class A or B depending on measurement function, IEEE519, IEEE1159, IEEE1459 and EN50160
	Clock/calendar	Leap years, 24-hour clock
	Real-time clock accuracy	Not more than ± 1 s/day
	Internal memory capacity for data	At least 2 GB
	Maximum recording period	At least 31 days
	Measurement time control	Automatic
	Maximum number of events	Limited only by the size of the internal memory
	Power requirements	100 to 240 Vrms $\pm 10\%$, 47-63 Hz, 40 W
	Operating time during interruptions (internal UPS operation)	5 minutes per interruption, 60 minutes total operating time without recharging
	Dimensions	215 x 310 x 35 mm (8.5 x 12.2 x 3.5 in)
	Mass (weight)	6.3 kg (14 lb)

Input	Measurement types	One Phase Plus Neutral, One Phase IT No Neutral, One Phase Split Phase, Three Phase Wye, Three Phase Delta, Three Phase IT, Three Phase High Leg, Three Phase Open Leg, 2 Element Delta, 2 1/2 Element Wye
	Input channels	Voltage: 4 channels, AC/DC
		Current: 5 channels
	Voltage channels	Input resistance: 2 M Ω
		Input capacitance: < 20 pF
Current input characteristics	2 Vrms = full scale, 1 M Ω Input Impedance for ferro CTs, low impedance for Flexi-CTs	
Measuring method	Simultaneous digital sampling of voltage and current. Digital PLL synchronized sampling, internal frequency reference used during voltage drops.	
Synchronization and sampling	PLL-synchronization source	The PLL synchronizes to the A-N voltage for wye power types, and to the A-B voltage for delta power types. All listed power types can be characterized as either wye or delta.
	PLL lock range	42.5 to 69 Hz
	Sampling frequency	Voltage and current: 256 samples/cycle Inter-harmonics per IEC 61000-4-7: 2 560 points/10 cycles (50 Hz), 3072 points/12 cycles (60 Hz) Transient Voltage: 5 MHz
	A/D resolution	Voltage and current: 24 bits
Transient voltage: 14 bits		
Voltage and current measurements	Voltage measurement range	AC voltage: 1000 Vrms \pm 10% over range DC voltage: \pm 1000 V +10% over range
	Voltage crest factor	3 or less
	Current measurement range	Depends on current probe used
	Current crest factor	4 or less
RMS voltage	Measurement type	True RMS calculated continuously: every cycle, every 1/2 cycle, and every 10 or 12 cycles at 50 or 60 Hz respectively, as required by IEC 61000-4-30.
	Measurement uncertainty	AC: \pm 0.2% reading \pm 0.1% full scale, above 50 Vrms DC: \pm 0.5% reading \pm 0.2% full scale, above 50 VDC
RMS current	Measurement type	True RMS calculated continuously: every cycle, every 1/2 cycle, and every 10 or 12 cycles at 50 or 60 Hz respectively, as required by standards
Transient voltage (impulse)	Measurement type	Waveshape sampling
	Full scale	8000 V pk
	Sample resolution	200 nS
	Measurement uncertainty	\pm 5% reading \pm 20 V (test parameters: 1000 VDC, 1000 Vrms, 100 kHz)

Voltage swell (rms swell)	Measurement type	True RMS (one cycle calculation by overlapping each half cycle - voltage between lines is measured for 3P3W lines and phase voltage is measured for 3P4W lines)
	Displayed data	Amplitude and duration of swell
	Measurement	Same as rms voltage
Voltage dip (rms sag)	Measurement type	True RMS (one cycle calculation by overlapping each half cycle - voltage between lines is measured for 3P3W lines and phase voltage is measured for 3P4W lines)
	Displayed data	Amplitude and duration of dip or interruption
	Measurement	Same as rms voltage
Voltage dropout (interruption)	Measurement type	Same as voltage dip
LAN interface	Connector	RJ-45
	Speed and type	10/100 Base-T, auto MDIX
	Communications protocol	TCP/IP over Ethernet
Wireless controller interface	Connection	wireless (2.4 GHz radio)
	Speed	up to 700 kbit/second
	Communications protocol	Bluetooth SPP
Power Measurements		
Power, battery life	Measurement type	True RMS calculated continuously: every cycle, and every 10 or 12 cycles at 50 or 60 Hz respectively, as required by standards
Frequency	Measurement range	42.5 to 69 Hz
	Measurement source	Same as PLL synchronization source
	Measurement accuracy	±10 mHz (10 to 110% of range, with sine wave)
Power factor	Measurement range	0.000 to 1.000
	Measurement accuracy	±1 digit from the calculation of each measured value (±3 digits for total)
Displacement power factor	Measurement method	Calculated from the phase difference between voltage fundamental and current fundamental
	Measurement range	- 1.000 (leading) to + 1.000 (lagging)
	Measurement accuracy	±0.5% reading ±2% full scale ±1 digit
Voltage unbalance and phase sequence	Measurement method	Positive sequence voltage divided by negative sequence voltage, per IEC 61000-4-30

Harmonic voltage and current	Analysis window	rectangular
	Analysis order	1st to 50th order
	Measurement accuracy	Voltage / Current: 1st to 20th orders: $\pm 0.5\%$ reading $\pm 0.2\%$ full scale, 21st to 50th orders: $\pm 1\%$ reading $\pm 0.3\%$ full scale (current sensor accuracy must be included for current and power)
	Measurement method	IEC 61000-4-7
Inter-harmonic voltage and current (intermediate harmonics)	Analysis window	rectangular
	Analysis orders	1.5 to 49.5th order
	Measurement method	IEC 61000-4-7
Flicker	Measurement method	IEC 61000-4-15
		Plt for 2 hours and PSt for 10 minutes
	Measuring range	0,1 to 5 (25) depending on voltage level, modulation and frequency
Environmental Specifications		
Environmental	Operating environment	Indoors or in covered area outdoors, up to 2 000 m altitude
	Storage temperature and humidity	-20°C to 50°C, 80% RH max, non-condensing
	Operating temperature and humidity	0°C to 40°C, 80% RH max, non-condensing
Maximum rated working voltage	Voltage terminals	1100 Vrms
	Voltage durability	5550 Vrms AC for 1 minute, between voltage input terminals, voltage input terminals and current probes, and voltage input terminals and case (50/60 Hz, 1 mA sense current)
	Enclosure protection	IP30 (per EN 60529)
Standards	EMC	EN 61326-1:1997+A1:1998 Class A
		EN 61000-3-2:1995+A1:1998+A2:1998
		EN 61000-3-3:1995
	Safety	EN 61010-1 2 nd Edition; 2 000
		Voltage input unit: Contamination Level 2 , Overvoltage Category 1000 V CAT III, 600 V CAT IV (anticipated overvoltage: 8000 V)

Ordering information



Fluke 1750/B

Fluke 1750/B Three-Phase Basic Power Quality Recorder

Includes:

- Three-Phase Power Recorder
- 1750 acquisition unit
- ARCHOS 43 Internet Tablet
- 5 Test leads and clips
- 2GB SD Memory card (larger cards not compatible)
- Fluke Power View and Fluke Power Analyze software
- Power cord with international plug set
- Ethernet cable
- Color localization set
- Printed Getting Started manual
- Product CD with software and user manual PDF
- CS 1750/1760 Rugged transit softcase

Fluke. *Keeping your world up and running.®*

Fluke Corporation

PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa

+31 (0)40 267 5100

In Canada (905) 890-7600

From other countries +1 (425) 446-5500

Representative office of Fluke South East Asia Pte Ltd

C/O Danaher Vietnam

Green Power Tower, 11th Floor Unit 2

35 Ton Duch Thang Street, District 1

Ho Chi Minh City

Vietnam

Tel: +84-8-2220-5371 (ext 103)

Email: info.asean@fluke.com

www.fluke.com/vn-vi

©2021 Fluke Corporation. Specifications subject to change without notice.

12/2021

Modification of this document is not permitted without written permission from Fluke Corporation.