

Fluke FlukeView® Forms Software with Cable



Key features

With FlukeView® Forms documenting software, the logging capabilities of handheld test equipment can be used to solve tough problems. You can download the readings from meters into FlukeView® Forms to spot trends and document measurement data.

You can instantly review and compare data from up to 6 different meters† on the same document - providing analysis capabilities that a meter alone can't provide.

FlukeView® Forms comes with an array of standard analysis and reporting forms that get you started on displaying your data in tables, graphs or helpful diagrams. You can leave notes on the forms to draw attention to a particular event.†

Or use the FlukeView® Forms Plus Designert to customize your reports or add your company logo.

FlukeView® Forms communicates with supported tools fast and easily via an infrared serial interface. The software will automatically recognize your meter and transfer the data without any configuration.

Share or store your data with co-workers or clients – print forms, export to other software programs, or have co-workers and clients download the free FlukeView® Demo/Reader to view and interact with your captured data.

FlukeView Forms Compatibility Chart

FVF Option	Instrument	Cable	Application Level
------------	------------	-------	-------------------

FVF-UG	Software only upgrade, from FVF Basic to FlukeView Forms plus Designer**	No Cable included	FlukeView Forms plus Designer
FVF-SC2	Fluke 280 Series, 53-II B and 54-II B, 789, 1550B, 1653, 180 Series*	USB / IR	FlukeView Forms plus Designer
FVF-SC4	Fluke 8808A, 8845A, 8846A, 45*	USB / Serial	
FVF-BASIC	Fluke 280 Series, 789, 1550B, 1653, 180 Series*	USB / IR	FVF BASIC
FVF-SC5	Software only**	No Cable included	

* Obsolete

** For all instruments listed in table

Using FlukeView® Forms with Multimeters, Thermometers†, MegOhmmeters and ProcessMeter™ tools

For the meters in the table below, you can measure and store hundreds of readings to the meter's internal memory, and then later download the information to FlukeView® Forms. For meters that do not have internal memory, such as the Fluke-187, Fluke-789 and the Fluke-45, you can take interactive readings while connected to your PC with FlukeView® Forms.

FlukeView® Forms also logs events to make analyzing your data easier. This unique method of data recording provides more detailed readings when the input signal changes significantly. The amount of signal change that will trigger an event can be adjusted to fit your specific test situation. The minimum, maximum and average of readings are recorded for each event. Logging sessions can also be configured so that data will be recorded over specific intervals (e.g., every 5 minutes or 30 seconds).

Using FlukeView® Forms with Fluke 1653B Installation tester†

Up to 500 test results can be stored in the Fluke 1653B installation tester. The data stored for each measurement consists of the test function, user selectable test conditions and unique references. The results can be uploaded for preparing professional reports. These reports can easily be customized to suit individual requirements as well as compliance with local regulations. Standard formats as well as localized forms for Germany (ZVEH), Austria (ÖVE) and Switzerland (electrosuisse, gem. NIV) are also available

† Not supported in FlukeView Forms Basic

Product overview: Fluke FlukeView® Forms Software with Cable

Expand the power of the world's most rugged, accurate handheld test tools with FlukeView® Forms Documenting Software.

To address the increasing demands for reporting and documentation, Fluke presents FlukeView Forms documenting software. FlukeView Forms increases the power of your Fluke tool by enabling you to document, store and analyze individual readings or series of measurements, then convert them into professional looking documents.

Several versions of the product are available, depending upon the type of cable needed to download data from your instrument and depending upon the data reporting capability you need. FlukeView Forms offers two levels of capability: FlukeView Forms Basic, and FlukeView Forms plus Designer. FlukeView Forms Basic can be used alone to download measurement data and create reports that can be saved and printed. FlukeView Forms plus Designer allows a user to edit an existing form or create a new form to customize the report to individual needs. A common edit might add a company logo and title. See the [Features] tab on this page for more information.

Capability Comparison

Capabilities	FlukeView® Forms Basic	FlukeView® Forms plus Designer
Transfer data points from your meter to your PC	X	X
Number of standard forms	2	9
Able to modify standard forms	No	Yes
Includes FlukeView® Forms Designer for customizing forms	No	Yes

Number of multiple meters whose data can be viewed simultaneously	1	8
Number of concurrently running instances of FlukeView Forms allowed	1	4
Ability to change company name on report	No	Yes
Supports multi-page forms	No	Yes

FlukeView Forms supports the following test tools:

- Fluke 1550B MegOhmMeter
- Fluke 1653 / 1653B / 1654B / 1662 / 1663 / 1664FC Electrical Installation Tester
- Fluke 180 series
- Fluke 287 and 289
- Fluke 45
- Fluke 53-II B and 54-II B
- Fluke 568 IR Thermometer
- Fluke 789 ProcessMeter
- Fluke 8808A
- Fluke 8845A/8846A
- Fluke 89-IV and 87-IV
- Fluke 975 AirMeter Test Tool
- Fluke 983 Particle Counter

The ability of FlukeView Forms to support multiple instruments enables the user to install and learn only one software application in order to use these multiple tools fully.

Select the appropriate model number below based upon your requirements:

Model Number	Description	Cable	Application Level
FVF-UG	Software only upgrade, from FVF Basic to FlukeView Forms plus Designer**	No Cable included	
FVF-SC2	Fluke 280 Series, 53-II B and 54-II B, 789, 1550B, 1653, 180 Series*	USB / IR	FlukeView Forms plus Designer
FVF-SC4	Fluke 8808A, 8845A, 8846A, 45*	USB / Serial	
FVF-BASIC	Fluke 280 Series, 789, 1550B, 1653, 180 Series*	USB / IR	FlukeView Forms BASIC
FVF-SC5	Software only**	No Cable included	

* Obsolete

** For all instruments listed in table

FlukeView® Forms Basic (FVF-BASIC): Owners of Fluke 280 series, 180 series, 789 and 1550B, who do not need the full power of FlukeView forms, can use FlukeView® Basic version. Transfer data points from your meter to your PC and use the two standard, non-customizable forms to display your readings in table or graphical form. For a larger array of forms or to use FlukeView® Forms Designer to customize your forms, upgrade to FlukeView® Forms version 3.3 with FVF-UG.

FlukeView® Forms Upgrade (FVF-UG): You can expand the power of your Fluke Test Tools by upgrading from FlukeView Forms Basic with the FlukeView® Forms Software Upgrade.

With the FlukeView® Forms Software Upgrade you can:

Instantly review and compare data from up to 6 different meters on the same document - providing analysis capabilities that a meter alone can't provide.

Use the array of Upgraded analysis and reporting forms to display your data in tables, graphs or helpful diagrams; even leave notes on the forms to draw attention to a particular event.

Or use the FlukeView® Forms plus Designer to customize your reports or add your company logo.




Specifications: Fluke FlukeView® Forms Software with Cable

Specifications	
Operating system for FlukeView Forms	Windows 2000, Windows XP, Windows Vista, Windows 7, Windows 8 or Windows 10
Minimum PC hardware	Pentium class or better microprocessor
	32 MB RAM
	70 MB hard disk space (100 MB to install)
	Serial or USB port
Mechanical and General Specifications	
Size	203 x 100 x 50 mm
Weight	545 g

Administrator Privileges required to install software on Windows 2000, XP, or Windows Vista

Ordering information



Fluke FlukeView Forms

Fluke. *Keeping your world up and running.®*

Fluke Corporation

PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa

+31 (0)40 267 5100

In Canada (905) 890-7600

From other countries +1 (425) 446-5500

Representative office of Fluke South East Asia Pte Ltd

C/O Danaher Vietnam

Green Power Tower, 11th Floor Unit 2

35 Ton Duch Thang Street, District 1

Ho Chi Minh City

Vietnam

Tel: +84-8-2220-5371 (ext 103)

Email: info.asean@fluke.com

www.fluke.com/vn-vi

©2021 Fluke Corporation. Specifications subject to change without notice.

12/2021

Modification of this document is not permitted without written permission from Fluke Corporation.